

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, 4-position, PUR halogen-free, red lilac RAL 4001, shielded, Plug straight M12, coding: B, on Socket straight M12, coding: B, cable length: 2 m

Commercial data

Item number	1416298
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF19
Product key	AF1CDD
GTIN	4055626067629
Weight per piece (including packing)	148.9 g
Weight per piece (excluding packing)	148.9 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	B

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

Type	Plug straight M12
Number of positions	4
Coding type	B (Standard)

Connection 2

Type	Socket straight M12
------	---------------------

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Number of positions	4
Coding type	B

Cable/line

Cable length	2 m
--------------	-----

CANopen®/DeviceNet™, PUR, violet [920]

Dimensional drawing		
UL AWM Style	21198 (80°C/300 V)	
Number of positions	4	
Shielded	yes	
Cable type	CANopen®/DeviceNet™, PUR, violet [920]	
Conductor structure	2xAWG24/19+2xAWG22/19	
AWG signal line	24	
AWG power supply	22	
Conductor cross-section	2x 0.25 mm² (Data cable)	
	2x 0.34 mm² (Power supply)	
	1x 0.34 mm² (Drain wire)	
Wire diameter incl. insulation	1.95 mm ±0.05 mm (Data cable)	
	1.4 mm ±0.05 mm (Power supply)	
External cable diameter	6.70 mm ±0.3 mm	
Outer sheath, material	PUR	
External sheath, color	red lilac RAL 4001	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	Foamed PE (Data cable)	
	PE (Power supply)	
Single wire, color	red-black, blue-white	
Twisted pairs	2 cores to the pair	
Overall twist	2 pairs around a drain wire in the center to the core	
Optical shield covering	80 %	
Insulation resistance	≥ 5 GΩ*km (Data cable)	
	≥ 5 GΩ*km (Power supply)	
Wave impedance	120 Ω ±10 % (with 1 MHz)	
Nominal voltage, cable	≤ 300 V (Peak value, not for high-power applications)	
Test voltage Core/Core	2000 V (50 Hz, 1 min.)	
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)	
Minimum bending radius, fixed installation	4 x D	

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s², Ambient temperature: -20 °C ... 60 °C
Shield attenuation	≤ 22.9 dB/km (with 1 MHz)
	≤ 16.4 dB/km (At 500 kHz)
	≤ 9.5 dB/km (At 125 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Special properties	Flexible cable conduit capable
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 75 °C (Cable, flexible installation)

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight, shielded

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 10.0	EC002599
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M12MSB/ 2,0-920/FSB X2X - Bus system cable



1416298

<https://www.phoenixcontact.com/us/products/1416298>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	5.226 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com