

# VS-OE-OE-94A-100,0 - Data cable



1416305

<https://www.phoenixcontact.com/us/products/1416305>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Data cable, Ethernet CAT5 (1 Gbps), shielded, PUR halogen-free, water blue RAL 5021, 8-wire (4x2xAWG24/1, SF/UTP), color single wire: white/blue-blue, white/orange-orange, white/green-green, white/brown-brown, cable length: 100 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1416305       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF11          |
| Product key                          | AF1LFA        |
| GTIN                                 | 4046356473545 |
| Weight per piece (including packing) | 5,242 g       |
| Weight per piece (excluding packing) | 5,023 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# VS-OE-OE-94A-100,0 - Data cable

1416305

<https://www.phoenixcontact.com/us/products/1416305>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable by the meter |
| Application         | Standard                |
| Number of positions | 8                       |
| Shielded            | yes                     |

### Electrical properties

|                     |        |
|---------------------|--------|
| Transmission medium | Copper |
| Transmission speed  | 1 Gbps |


### Interfaces

|                      |                                   |
|----------------------|-----------------------------------|
| Bus system           | Ethernet                          |
| Signal type/category | Ethernet CAT5 (IEC 11801), 1 Gbps |

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 100 m |
|--------------|-------|

### Ethernet [94A]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| UL AWM Style                    | 21238 (80 °C / 600 V)  |
| Number of positions             | 8  |
| Shielded                        | yes  |
| Cable type                      | Ethernet [94A]   |
| Conductor structure             | 4x2xAWG24/1, SF/UTP  |
| Conductor structure signal line | 1x 0.51 mm   |
| AWG signal line                 | 24   |
| Conductor cross-section         | 4x 2x 0.25 mm <sup>2</sup>   |
| Wire diameter incl. insulation  | 1.02 mm ±0.03 mm   |
| External cable diameter         | 6.30 mm ±0.2 mm  |
| Outer sheath, material          | PUR  |
| External sheath, color          | water blue RAL 5021  |
| Conductor material              | Bare Cu wire   |
| Material wire insulation        | PE   |
| Single wire, color              | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown           |

# VS-OE-OE-94A-100,0 - Data cable



1416305

<https://www.phoenixcontact.com/us/products/1416305>

|                                 |  |
|---------------------------------|--|
| Twisted pairs                   | 2 cores to the pair  |
| Overall twist                   | 4 pairs for core   |
| Optical shield covering         | 85 %   |
| Insulation resistance           | $\geq 5 \text{ G}\Omega\cdot\text{km}$   |
| Wave impedance                  | $100 \Omega \pm 15 \Omega$ (at 1 ... 100 MHz)  |
| Nominal voltage, cable          | $\leq 600 \text{ V}$   |
| Test voltage Core/Core          | 2000 V ((50 Hz/1 min))   |
| Test voltage Core/Shield        | 2000.00 V ((50 Hz/1 min))  |
| Halogen-free                    | according to IEC 60754-1   |
| Flame resistance                | according to IEC 60332-1-2<br>UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2) |
| Resistance to oil               | in accordance with DIN EN 60811-404  |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)   |

# VS-OE-OE-94A-100,0 - Data cable



1416305

<https://www.phoenixcontact.com/us/products/1416305>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003249 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# VS-OE-OE-94A-100,0 - Data cable



1416305

<https://www.phoenixcontact.com/us/products/1416305>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 62.276 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)