


VS-OE-OE-93A-100,0 - Data cable



1416392

<https://www.phoenixcontact.com/us/products/1416392>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Data cable, PROFINET CAT5 (100 Mbps), shielded, PVC, green-yellow RAL 6018, 4-wire (1x4xAWG22/1, SF/TQ), color single wire: white, yellow, blue, orange, cable length: 100 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1416392 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF11 |
| Product key | AF1LFA |
| GTIN | 4046356474313 |
| Weight per piece (including packing) | 6,094 g |
| Weight per piece (excluding packing) | 6,094 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

VS-OE-OE-93A-100,0 - Data cable

1416392

<https://www.phoenixcontact.com/us/products/1416392>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable by the meter |
| Application | Standard |
| Number of positions | 4 |
| Shielded | yes |

Electrical properties

| | |
|---|-----------------------|
| Transmission medium | Copper |
| Transmission speed | 100 Mbps |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |


Interfaces

| | |
|----------------------|-------------------------------------|
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps |
|----------------------|-------------------------------------|

Cable/line

| | |
|--------------|-------|
| Cable length | 100 m |
|--------------|-------|

PROFINET [93A]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| UL AWM Style | 21695 (80 °C / 600 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PROFINET [93A] |
| Conductor structure | 1x4xAWG22/1, SF/TQ |
| Conductor structure signal line | 1x 0.64 mm |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² |
| Wire diameter incl. insulation | 1.45 mm ±0.15 mm |
| External cable diameter | 6.50 mm ±0.2 mm |
| Outer sheath, material | PVC |
| External sheath, color | green-yellow RAL 6018 |
| Material wire insulation | PE |
| Single wire, color | white, yellow, blue, orange |
| Overall twist | Star quad |
| Optical shield covering | 85 % |

VS-OE-OE-93A-100,0 - Data cable



1416392

<https://www.phoenixcontact.com/us/products/1416392>

| | |
|---------------------------------|--|
| Insulation resistance | $\geq 5 \text{ G}\Omega \cdot \text{km}$ |
| Wave impedance | $100 \Omega \pm 15 \Omega$ (at 1 ... 100 MHz) |
| Nominal voltage, cable | $\leq 600 \text{ V}$ |
| Test voltage Core/Core | 2000 V ((50 Hz/1 min)) |
| Test voltage Core/Shield | 2000.00 V ((50 Hz/1 min)) |
| Flame resistance | UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1) |
| | UL 1685 (CSA FT 4) |
| | UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2) |
| Resistance to oil | OIL RES I according to UL 2256 |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |

VS-OE-OE-93A-100,0 - Data cable



1416392

<https://www.phoenixcontact.com/us/products/1416392>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003249 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

VS-OE-OE-93A-100,0 - Data cable



1416392

<https://www.phoenixcontact.com/us/products/1416392>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|----------------|
| CO2e kg | 47.076 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com