

FOC-OP4S-OP4S-GL01/10 - Connecting cable



1415228

<https://www.phoenixcontact.com/us/products/1415228>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 4



Product description

Robust connecting cable ODC-4 to ODC-4, with screw connection, degree of protection: IP68

Your advantages

- Compact design with ceramic contact inserts
- Threaded locking latch
- For extreme ambient conditions

Commercial data

Item number	1415228
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAA
GTIN	4055626188393
Weight per piece (including packing)	465 g
Weight per piece (excluding packing)	460 g
Customs tariff number	85447000
Country of origin	CN

FOC-OP4S-OP4S-GL01/10 - Connecting cable



1415228

<https://www.phoenixcontact.com/us/products/1415228>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4

Interfaces

Signal	Ethernet
--------	----------

Electrical properties

Attenuation	typ. 0.2 dB
	max. 0.6 dB
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	800 N
---------------------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Ferrule material	TPU
Outer sheath, material	TPU

Connector

Connection 1

Locking type	Screw locking mechanism
Handle color	black
Insertion/withdrawal cycles	1000
Degree of protection	IP68 (IEC 60529) IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

Connection 2

Locking type	Screw locking mechanism
Handle color	black
Insertion/withdrawal cycles	1000
Degree of protection	IP68 (IEC 60529)
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

Cable/line

Cable length	10 m
Cable weight	26.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Outer sheath, material	TPU

FOC-OP4S-OP4S-GL01/10 - Connecting cable



1415228

<https://www.phoenixcontact.com/us/products/1415228>

External sheath, color	black
Individual wire diameter	250 µm
Tensile strength short-term/long-term	800 N
Halogen-free	complying with IEC 60754-1/2

FO cable

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Attenuation	typ. 0.2 dB
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	100g, according to IEC 61300-2-9

FOC-OP4S-OP4S-GL01/10 - Connecting cable



1415228

<https://www.phoenixcontact.com/us/products/1415228>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 9.0	EC002607
----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

FOC-OP4S-OP4S-GL01/10 - Connecting cable



1415228

<https://www.phoenixcontact.com/us/products/1415228>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com