

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Pin, straight, M12, T-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1418341       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 60 pc         |
| Sales key                            | AB23          |
| Product key                          | ABQAGD        |
| GTIN                                 | 4055626170664 |
| Weight per piece (including packing) | 7.48 g        |
| Weight per piece (excluding packing) | 3.577 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|--|

### Product properties

|                       |                |
|-----------------------|----------------|
| Product type          | Contact insert |
| Application           | Power          |
| Sensor type           | Power          |
| Number of positions   | 4              |
| No. of power contacts | 4              |
| Seal present          | yes            |
| Shielded              | yes            |
| Coding                | T              |
| Thread type           | M12            |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                       |        |
|-----------------------|--------|
| Rated surge voltage   | 1.5 kV |
| Contact resistance    | ≤ 3 mΩ |
| Insulation resistance | ≥      |
| Nominal voltage $U_N$ | 63 V   |
| Nominal current $I_N$ | 12 A   |

### Connection data

|                   |                       |
|-------------------|-----------------------|
| Connection method | THR solder connection |
|-------------------|-----------------------|

### Interfaces

|                      |       |
|----------------------|-------|
| Signal type/category | Power |
|----------------------|-------|

### Material specifications

|  |      |
|--|------|
| Material Insulating body               | PA   |
| Material Contact                       | CuZn |
| Material Contact surface               | Au   |
| Material Seal                          | FKM  |
| Flammability rating according to UL 94 | V0   |

### Connector

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Pin      |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | T        |

## Cable/line

|                      |       |
|----------------------|-------|
| Signal type/category | Power |
|----------------------|-------|

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|   |   |
|---|---|
| Degree of protection  | IP67 (correctly plugged in and locked)                                |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 105 °C<br>-40 °C ... 105 °C (without mechanical actuation) |
| UL Type Rating  | Type 4 (indoor use only)  |

## Packaging specifications

|                   |                   |
|-------------------|-------------------|
| Type of packaging | Belt              |
| Delivery state    | with assembly pad |


# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier

1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Drawings

Schematic diagram



Connector pin assignment of M12 plug, 4-pos., T-coded, view of pin side

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier





1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418341>

|  <b>cUL Recognized</b><br>Approval ID: E468743-20190917 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 63 V                  | 12 A                  | 16                | -                           |

|  <b>UL Recognized</b><br>Approval ID: E468743-20190917 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 63 V                  | 12 A                  | 16                | -                           |

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440223 |
| ECLASS-15.0 | 27440223 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003557 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-CI-M12MST-4CON-L180 TOR SH - Contact carrier



1418341

<https://www.phoenixcontact.com/us/products/1418341>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)