

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PROFINET patch cable, shielded, star quad, 22 AWG stranded (19-wire), green, straight RJ45 connector / IP20, to straight RJ45 connector / IP20, length: 2 m

PROFINET patch cable

## Commercial data

Item number	1418387
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB11
Product key	ABNABA
GTIN	4046356534611
Weight per piece (including packing)	152 g
Weight per piece (excluding packing)	141.96 g
Customs tariff number	85444210
Country of origin	PL

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Sensor type	PROFINET
Number of positions	4
Connection profile	RJ45 8(4)
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Degree of pollution	1
---------------------	---

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Transmission speed	100 Mbps

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

### Material specifications

Flammability rating according to UL 94	V2
Housing material	PA 6.6
Contact material	CuSn
Contact surface material	Ni/Au

### Connector

#### Connection 1

Type	Plug straight RJ45
Shielded	yes
Degree of protection	IP20

#### Connection 2

Type	Plug straight RJ45
Shielded	yes

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

## Cable/line

Cable length	2.00 m
--------------	--------

### PROFINET drag chain CAT5 [93C]

Number of positions	4
Shielded	yes
Cable type	PROFINET drag chain CAT5 [93C]
Conductor structure	1x4xAWG22/19, S/TQ
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	4x 0.38 mm <sup>2</sup>
Wire diameter incl. insulation	1.5 mm 0.1 mm
External cable diameter	6.50 mm
Outer sheath, material	PUR
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Single wire, color	white, yellow, blue, orange
Wave impedance	100 Ω ±15 Ω (at 1 ... 100 MHz)
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 60 mm, Traversing rate: 3 m/s, Acceleration: 3 m/s <sup>2</sup>

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418387>



**EAC**

Approval ID: 19060508

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-PNRJ45-PNRJ45-93C-2,0 - Patch cable



1418387

<https://www.phoenixcontact.com/us/products/1418387>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)