

# SACC-CIP-M8MS-4P SMD-SP - Sample set



1418666

<https://www.phoenixcontact.com/us/products/1418666>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sample set, 4-position, Pin, straight, M8, A-coding, SMD reflow



## Commercial data

Item number	1418666
Packing unit	5 pc
Minimum order quantity	5 pc
Product key	ABQXAA
GTIN	4055626163208
Weight per piece (including packing)	6.98 g
Weight per piece (excluding packing)	2.661 g
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Number of positions	4
Seal present	yes
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\leq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	3 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

### Connector

#### Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M8
Coding	A

### Mechanical properties

#### Mechanical data

# SACC-CIP-M8MS-4P SMD-SP - Sample set



1418666

<https://www.phoenixcontact.com/us/products/1418666>

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection (not plugged in)	IP65 (not plugged in, by means of additional O-ring seal with device)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C (Plug / socket)
	-40 °C ... 105 °C (without mechanical actuation)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

# SACC-CIP-M8MS-4P SMD-SP - Sample set


1418666

<https://www.phoenixcontact.com/us/products/1418666>



## Drawings

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

# SACC-CIP-M8MS-4P SMD-SP - Sample set



1418666

<https://www.phoenixcontact.com/us/products/1418666>

## Classifications

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CIP-M8MS-4P SMD-SP - Sample set



1418666

<https://www.phoenixcontact.com/us/products/1418666>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)