

# VS-BU/C6-IP67/B-94F-LI/5,0 - Network cable



1415856

<https://www.phoenixcontact.com/us/products/1415856>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled Ethernet cable, CAT6, shielded, 4-pair, AWG 26 stranded (7-wire), RAL 5021 (water blue), RJ45 socket module/IP20 for Freenet system, 8-pos. on RJ45 plug/IP67, black, line, length 5 m

## Commercial data

Item number	1415856
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNABF
GTIN	4046356474993
Weight per piece (including packing)	265.8 g
Weight per piece (excluding packing)	257.105 g
Country of origin	PL

1415856

<https://www.phoenixcontact.com/us/products/1415856>

## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL IE8 CAT6A
Number of positions	8
Shielded	yes

### Interfaces

Signal type/category	Ethernet CAT6, 1 Gbps
----------------------	-----------------------

### Electrical properties


Transmission speed	1 Gbps
Transmission characteristics (category)	CAT6
Transmission speed	1 Gbps
Wave impedance	100 Ω

### Material specifications

Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

### Connector

#### Connection 1

Dimensional drawing	 <p>Connector pin assignment plug RJ45</p>
Type	RJ45 Plug, straight, 8-position, Snap-in locking
Number of positions	8
Signal type/category	Ethernet CAT6 (IEC 11801:2002), 1 Gbps
Insertion/withdrawal cycles	≥ 750
Insertion force	30 N (per signal contact)
Withdrawal force	50 N (per signal contact)
Degree of pollution	2
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PC
Color (Housing)	black

# VS-BU/C6-IP67/B-94F-LI/5,0 - Network cable




1415856

<https://www.phoenixcontact.com/us/products/1415856>

Flammability rating according to UL 94	V2
Degree of protection	IP67
	IP65
Ambient temperature (operation)	-40 °C ... 60 °C


## Connection 2

Dimensional drawing	 <p>Connector pin assignment plug RJ45</p>
Type	RJ45 Socket, straight, 8-position, Freenet
Number of positions	8
Signal type/category	Ethernet CAT5 (IEC 11801:2002), 100 Mbps
Insertion/withdrawal cycles	≥ 750
Insulation resistance	> 500 MΩ
Overvoltage category	I
Degree of pollution	1
Material Contact	Copper alloy
Material Contact surface	Au
Material Contact carrier	PC
Color (Housing)	silver-colored
Flammability rating according to UL 94	V0
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 70 °C

## Cable/line

Cable length	5.00 m
--------------	--------

## Ethernet 10 Gbit [94F]

Dimensional drawing	
UL AWM Style	21238 (80 °C / 600 V)
Number of positions	8
Shielded	yes

# VS-BU/C6-IP67/B-94F-LI/5,0 - Network cable



1415856

<https://www.phoenixcontact.com/us/products/1415856>

Cable type	Ethernet 10 Gbit [94F]
Conductor structure	4x2xAWG26/7; S/FTP
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	1 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Optical shield covering	70 %
Insulation resistance	≥ 500 MΩ*km
Loop resistance	≤ 290.00 Ω/km
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	51 mm
Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2
	in accordance with UN ECE-R 118.03
	according to CSA C 22.2 No. 210-FT1
Resistance to oil	in accordance with DIN EN 60811-404
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (cable, fixed installation)
	-10 °C ... 50 °C (Cable, flexible installation)

# VS-BU/C6-IP67/B-94F-LI/5,0 - Network cable



1415856

<https://www.phoenixcontact.com/us/products/1415856>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415856>



**EAC**

Approval ID: 19060508

# VS-BU/C6-IP67/B-94F-LI/5,0 - Network cable



1415856

<https://www.phoenixcontact.com/us/products/1415856>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1415856

<https://www.phoenixcontact.com/us/products/1415856>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	859223c1-c0bc-4fac-88f8-7fb4b12814b1

### EF3.1 Climate Change

CO2e kg	6.197 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)