
CUC-F-J1ZNI-S/R4IDC8 - RJ45 jack insert

1418984

https://www.phoenixcontact.com/us/products/1418984

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.





RJ45 jack insert, RJ45, Ethernet, CAT6$_A$ (10 Gbps), 8-position, connection method: IDC connection, material: Metal, connection cross section: AWG 26- 22, degree of protection: IP20, Freenet design for use with IP67 panel mounting frame and terminal outlets

Product description

Freenet system

Your advantages

- Assembly without special tools
- Compact design
- Rugged design

Commercial data

Item number	1418984
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNACA
GTIN	4055626251431
Weight per piece (including packing)	20 g
Weight per piece (excluding packing)	20 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Product properties

Product type	Female insert
Type	RJ45
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Number of slots	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	III

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	0.8 kV
Frequency range	500 MHz
Insulation resistance	> 500 MΩ (100 V DC)
Nominal voltage U_N	72 V (DC)
Nominal current I_N	1.5 A
Transmission medium	Copper
Transmission speed	10 Gbps
Transmission characteristics (category)	$CAT6_A$
Power transmission	PoE+

Connection data

Connection technology

Connection method	IDC connection

Interfaces

Signal type/category	Ethernet $CAT6_A$, 10 Gbps

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	PC
Material, protective cover	PC

Cable/line

External cable diameter	4.5 mm ... 9 mm
Wire diameter	0.4 mm ... 0.65 mm
Wire diameter including insulation	0.8 mm ... 1.6 mm

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Mounting

Mounting type	Snap in

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1418984

cUL Recognized
Approval ID: E335024-DUXR8

UL Recognized
Approval ID: E335024-DUXR2

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440318

ETIM

ETIM 10.0	EC002597

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	1.494 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com