

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, degree of protection: IP67/IP20, cable length: 2 m, number of positions: 4, 100 Mbps, CAT5, cable outlet: straight, PROFINET, 1x4xAWG22/7, SF/TQ, green RAL 6018

## Commercial data

Item number	1416158
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNPAB
GTIN	4046356474238
Weight per piece (including packing)	169.4 g
Weight per piece (excluding packing)	156.782 g
Customs tariff number	85444210
Country of origin	PL

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

## Technical data

### Product properties

Product type	Circular connectors (device side)
Number of positions	4
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	PVC
Conductor material	Tin-plated Cu litz wires

### Electrical properties

Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Transmission speed	100 Mbps
Wave impedance	100 Ω

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

### Connector

#### Connection 1

Type	Flush-type female connector straight M12
Coding type	D
Shielded	yes
Insertion/withdrawal cycles	> 100
Degree of protection	IP67

#### Connection 2

Type	Plug straight RJ45
Shielded	yes
Degree of protection	IP20


### Cable/line

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

Cable length	2.00 m
PROFINET PVC stranded CAT5 [93B]	
Dimensional drawing	
Cable weight	67 kg/km
UL AWM Style	21694
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
Signal runtime	5.3 ns/m
Signal speed	0.66 c
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup>
Wire diameter incl. insulation	1.55 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Thickness, outer sheath	approx. 0.90 mm
Overall twist	Star quad
Optical shield covering	85 %
Insulation resistance	≥ 500 MΩ*km
Coupling resistance	≤ 20.00 mΩ/m (at 10 MHz)
Loop resistance	≤ 120.00 Ω/km
Wave impedance	100 Ω ±15 Ω (at 100 MHz)
Nominal voltage, cable	600 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	7 x D
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	46 mm
	80 dB (with 1 MHz)

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

Near end crosstalk attenuation (NEXT)	76 dB (at 4 MHz)
	70 dB (at 10 MHz)
	65 dB (at 16 MHz)
	63 dB (at 20 MHz)
	60 dB (at 31.25 MHz)
	55 dB (at 62.5 MHz)
	50 dB (at 100 MHz)
Shield attenuation	2.1 dB (with 1 MHz)
	4 dB (at 4 MHz)
	6.3 dB (at 10 MHz)
	8 dB (at 16 MHz)
	9 dB (at 20 MHz)
	11.4 dB (at 31.25 MHz)
	16.5 dB (at 62.5 MHz)
21.3 dB (at 100 MHz)	
Flame resistance	according to UL 1685 (CSA FT 4)
Resistance to oil	Resistant to oil to a limited extent
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 70 °C (cable, fixed installation)
	-40 °C ... 70 °C (Cable, flexible installation)
Ambient temperature (installation)	-20 °C ... 60 °C

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP67
	IP67/IP20
Ambient temperature (operation) (Cable, fixed installation)	-25 °C ... 60 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C ... 50 °C (Cable, flexible installation)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1416158>



**EAC**

Approval ID: 19060508

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

## Classifications

### ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

### ETIM

ETIM 10.0	EC003570
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-IP20-M12FSBP-93B-LI/2,0 - Network cable



1416158

<https://www.phoenixcontact.com/us/products/1416158>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	80687f88-6257-425f-a661-a536f58a2742

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)