

VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - RJ45 connector



1419182

<https://www.phoenixcontact.com/us/products/1419182>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP67, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, connection cross section: AWG 27- 24, cable outlet: straight, color: silver

Commercial data

Item number	1419182
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNMAA
GTIN	4046356539555
Weight per piece (including packing)	130.4 g
Weight per piece (excluding packing)	128.7 g
Customs tariff number	85366990
Country of origin	DE

1419182

<https://www.phoenixcontact.com/us/products/1419182>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	8
Number of slots	1
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps
Power transmission	PoE++ in accordance with: IEEE 802.3bt

Connection data

Connection technology

Connection method	IDC fast connection
Connection cross section AWG	27 ... 24 (flexible)
Conductor cross-section	0.11 mm ² ... 0.23 mm ²

Material specifications

Color	silver
Flammability rating according to UL 94	V0
Housing material	Metal
Cable seal material	PA/EPDM

Cable/line

External cable diameter	5 mm ... 10 mm
External cable diameter	5 mm ... 10 mm
Wire diameter	0.36 mm ... 0.51 mm
Cable cross section	0.13 mm ²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	750
-----------------------------	-----

VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - RJ45 connector



1419182

<https://www.phoenixcontact.com/us/products/1419182>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 70 °C

1419182

<https://www.phoenixcontact.com/us/products/1419182>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1419182

<https://www.phoenixcontact.com/us/products/1419182>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	3e60a736-399a-485f-ae31-38f5e9f867aa

EF3.1 Climate Change

CO2e kg	4.653 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com