

FOC-OP4S-OP4S-GL01/15 - Connecting cable



1419720

<https://www.phoenixcontact.com/us/products/1419720>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 4



Product description

Robust connecting cable ODC-4 to ODC-4, with screw connection, degree of protection: IP68

Your advantages

- Robust connector for 4 fibers, degree of protection: IP68 (when connected)
- For extreme ambient conditions

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1419720 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | ABNHAA |
| GTIN | 4055626187426 |
| Weight per piece (including packing) | 702.5 g |
| Weight per piece (excluding packing) | 627.5 g |
| Country of origin | CN |

FOC-OP4S-OP4S-GL01/15 - Connecting cable



1419720

<https://www.phoenixcontact.com/us/products/1419720>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 4 |

Electrical properties

| | |
|---------------------|-----------------------|
| Attenuation | typ. 0.2 dB |
| | max. 0.6 dB |
| Transmission medium | Multi-mode fiberglass |

Mechanical properties

| | |
|---------------------------------------|-------|
| Tensile strength short-term/long-term | 800 N |
|---------------------------------------|-------|

Material specifications

| | |
|--|-----|
| Flammability rating according to UL 94 | V0 |
| Ferrule material | TPU |
| Outer sheath, material | TPU |

Connector

Connection 1

| | |
|---------------------------------|-----------------------------------|
| Locking type | Screw locking mechanism |
| Handle color | black |
| Insertion/withdrawal cycles | 1000 |
| Degree of protection | IP68 (IEC 60529) |
| | IP68 |
| Ambient temperature (operation) | -40 °C ... 85 °C (IEC 61300-2-22) |

Connection 2

| | |
|---------------------------------|-----------------------------------|
| Locking type | Screw locking mechanism |
| Handle color | black |
| Insertion/withdrawal cycles | 1000 |
| Degree of protection | IP68 (IEC 60529) |
| Ambient temperature (operation) | -40 °C ... 85 °C (IEC 61300-2-22) |

Cable/line

| | |
|---------------------------------------|----------------------|
| Cable length | 15 m |
| Cable weight | 26.00 kg/km |
| Cable type | Multimode fiberglass |
| Cable type | Zip cord, fiberglass |
| Outer sheath, material | TPU |
| External sheath, color | black |
| Individual wire diameter | 250 µm |
| Tensile strength short-term/long-term | 800 N |

FOC-OP4S-OP4S-GL01/15 - Connecting cable



1419720

<https://www.phoenixcontact.com/us/products/1419720>

| | |
|--------------|------------------------------|
| Halogen-free | complying with IEC 60754-1/2 |
|--------------|------------------------------|

FO cable

| | |
|---------------------|----------------------------------|
| Number of fibers | 12 |
| Fiber | 62.5/125 µm OM1 |
| Fiber type | Multimode fiberglass 62.5/125 µm |
| Attenuation | typ. 0.2 dB |
| Transmission medium | Multi-mode fiberglass |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-----------------------------------|
| Degree of protection | IP68 |
| Ambient temperature (operation) | -40 °C ... 85 °C (IEC 61300-2-22) |
| Shock | 100g, according to IEC 61300-2-9 |

FOC-OP4S-OP4S-GL01/15 - Connecting cable



1419720

<https://www.phoenixcontact.com/us/products/1419720>

Classifications

ECLASS

ECLASS-13.0

27061003

ETIM

ETIM 9.0

EC000438

UNSPSC

UNSPSC 21.0

43223300

FOC-OP4S-OP4S-GL01/15 - Connecting cable



1419720

<https://www.phoenixcontact.com/us/products/1419720>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com