

VS-OE-OE-94D-100,0 - Data cable



1416334

<https://www.phoenixcontact.com/us/products/1416334>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Data cable, Ethernet CAT5 (1 Gbps), shielded, PVC (reinforced) UV-resistant, black RAL 9005, 8-wire (4x2xAWG26/7, SF/UTP), color single wire: white/blue-blue, white/orange-orange, white/green-green, white/brown-brown, cable length: 100 m

Commercial data

Item number	1416334
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356474559
Weight per piece (including packing)	5,102 g
Weight per piece (excluding packing)	5,071 g
Customs tariff number	85444290
Country of origin	DE

VS-OE-OE-94D-100,0 - Data cable



1416334

<https://www.phoenixcontact.com/us/products/1416334>

Technical data

Product properties

Product type	Data cable by the meter
Application	Standard
Sensor type	Ethernet
Number of positions	8
Shielded	yes

Electrical properties

Transmission medium	Copper
Transmission speed	1 Gbps


Interfaces

Signal type/category	Ethernet CAT5, 1 Gbps
----------------------	-----------------------

Cable/line

Cable length	100 m
--------------	-------

Ethernet [94D]

Dimensional drawing	
UL AWM Style	2464 (80°C/300 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet [94D]
Conductor structure	4x2xAWG26/7, SF/UTP
Signal speed	0.6 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	0.98 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PVC (reinforced) UV-resistant
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	white/blue-blue, white/orange-orange, white/green-green,

VS-OE-OE-94D-100,0 - Data cable



1416334

<https://www.phoenixcontact.com/us/products/1416334>

	white/brown-brown
Thickness, outer sheath	0.80 mm
Twisted pairs	2 cores to the pair
Overall twist	4 pairs, twisted
Optical shield covering	85 %
Max. conductor resistance	< 140 Ω/km
Insulation resistance	≥ 5 GΩ*km
Wave impedance	100 Ω ±15 Ω (at 4 ... 100 MHz)
Cable capacity	< 56 nF/km
Nominal voltage, cable	72 V DC
	300 V AC
Test voltage Core/Core	2500 V DC (2 s)
Test voltage Core/Shield	2500.00 V DC (2 s)
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Tensile strength	80 N
Flame resistance	According to VW-1
Resistance to oil	according to IEC 60811-2-1
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (installation)	0 °C ... 50 °C

VS-OE-OE-94D-100,0 - Data cable



1416334

<https://www.phoenixcontact.com/us/products/1416334>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-OE-OE-94D-100,0 - Data cable



1416334

<https://www.phoenixcontact.com/us/products/1416334>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	44.61 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com