

NBC-R4ACR/2,0-93M/R4ACR - Patch cable



1420386

<https://www.phoenixcontact.com/us/products/1420386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 4, 100 Mbps, CAT5, material: PA 6.6, PROFINET, 1x4xAWG22/7, SF/TQ, green RAL 6018

PROFINET patch cable

Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1420386 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | ABNABA |
| GTIN | 4055626206530 |
| Weight per piece (including packing) | 161.3 g |
| Weight per piece (excluding packing) | 140.831 g |
| Country of origin | PL |

1420386

<https://www.phoenixcontact.com/us/products/1420386>

Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Data cable preassembled |
| Product family | RJ45 INDUSTRIAL PN4 CAT5 |
| Number of positions | 4 |
| Number of slots | 1 |
| Shielded | yes |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution | 1 |

Interfaces

| | |
|----------------------|--|
| Signal type/category | PROFINET CAT5 (IEC 11801:2002), 100 Mbps |
|----------------------|--|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|---|-----------------------|
| Rated voltage (III/3) | 72 V (DC) |
| Rated current | 1.75 A |
| Nominal voltage U_N | 48 V |
| Nominal current I_N | 1 A |
| Transmission medium | Copper |
| Transmission speed | 100 Mbps |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |
| Transmission speed | 100 Mbps |

Mechanical properties

Mechanical data

| | |
|-------------------------------------|---------|
| Insertion force per signal contact | 50.00 N |
| Extraction force per signal contact | 30 N |

Material specifications

| | |
|--|--------|
| Flammability rating according to UL 94 | V2 |
| Housing material | PA 6.6 |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Outer sheath, material | PUR |

Connector

NBC-R4ACR/2,0-93M/R4ACR - Patch cable



1420386

<https://www.phoenixcontact.com/us/products/1420386>

Connection 1

| | |
|-----------------------------|---|
| Type | Plug angled RJ45 |
| Shielded | yes |
| Handle color | black |
| Material | CuSn (Contact) Ni/Au (Contact surface) PA (Contact carrier) PA (Housing) |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |


Connection 2

| | |
|-----------------------------|---|
| Type | Plug straight RJ45 |
| Shielded | yes |
| Handle color | black |
| Material | CuSn (Contact) Ni/Au (Contact surface) PA (Contact carrier) PA (Housing) |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |

Cable/line

| | |
|--------------|--------|
| Cable length | 2.00 m |
|--------------|--------|

PROFINET stranded CAT5 [93M]

| | |
|--------------------------------|--|
| Dimensional drawing |  |
| UL AWM Style | 21238 (80 °C / 600 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PROFINET stranded CAT5 [93M] |
| Conductor structure | 1x4xAWG22/7, SF/TQ |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² |
| Wire diameter incl. insulation | 1.56 mm ±0.05 mm |
| External cable diameter | 6.50 mm ±0.2 mm |
| Outer sheath, material | PUR |

NBC-R4ACR/2,0-93M/R4ACR - Patch cable



1420386

<https://www.phoenixcontact.com/us/products/1420386>

| | |
|---|---|
| External sheath, color | green RAL 6018 |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | PE |
| Single wire, color | white, yellow, blue, orange |
| Overall twist | Star quad |
| Optical shield covering | 85 % |
| Insulation resistance | $\geq 500 \text{ M}\Omega \cdot \text{km}$ |
| Loop resistance | $\leq 120.00 \text{ }\Omega/\text{km}$ |
| Wave impedance | $100 \text{ }\Omega \pm 15 \text{ }\Omega$ (at 100 MHz) |
| Nominal voltage, cable | $\leq 100 \text{ V}$ |
| Test voltage Core/Core | 2000 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 2000.00 V (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Halogen-free | according to IEC 60754-1 |
| Flame resistance | according to CSA C 22.2 No. 210-FT1 |
| Ambient temperature (operation) | -40 °C ... 80 °C -40 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-----------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 80 °C (RJ45 connector) |

NBC-R4ACR/2,0-93M/R4ACR - Patch cable

1420386

<https://www.phoenixcontact.com/us/products/1420386>



Drawings

Schematic diagram



Connector pin assignment plug RJ45

NBC-R4ACR/2,0-93M/R4ACR - Patch cable

1420386

<https://www.phoenixcontact.com/us/products/1420386>



Circuit diagram



Contact assignment of RJ45 plugs

NBC-R4ACR/2,0-93M/R4ACR - Patch cable



1420386

<https://www.phoenixcontact.com/us/products/1420386>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

NBC-R4ACR/2,0-93M/R4ACR - Patch cable



1420386

<https://www.phoenixcontact.com/us/products/1420386>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com