

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set



1420412

<https://www.phoenixcontact.com/us/products/1420412>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sample set, Universal, 4-position, Pin, straight, S-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1420412
Packing unit	5 pc
Minimum order quantity	5 pc
Product key	ABQAGO
GTIN	4055626224282
Weight per piece (including packing)	8.32 g
Weight per piece (excluding packing)	3.454 g
Country of origin	DE

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set



1420412

<https://www.phoenixcontact.com/us/products/1420412>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Number of positions	4
No. of power contacts	4
Coding	S
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	630 V
Nominal current I_N	12 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Universal
----------------------	-----------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

Connector

Connection 1

Head design	Pin
-------------	-----

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set



1420412

<https://www.phoenixcontact.com/us/products/1420412>

Head cable outlet	straight
Coding	S

Cable/line

Signal type/category	Universal
----------------------	-----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)


SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set

1420412

<https://www.phoenixcontact.com/us/products/1420412>

Drawings

Schematic diagram



Connector pin assignment of M12 plug, 4-pos., S-coded, view of pin side

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set





1420412

<https://www.phoenixcontact.com/us/products/1420412>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1420412>

 cUL Recognized Approval ID: E468743-20190917				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	12 A	16	-

 UL Recognized Approval ID: E468743-20190917				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	12 A	16	-

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set



1420412

<https://www.phoenixcontact.com/us/products/1420412>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12MSS-4CON-L180THR PE SP - Sample set



1420412

<https://www.phoenixcontact.com/us/products/1420412>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com