

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 2, power contacts: 2, control contacts: 0, Pin, Crimp connection, 2900 V/5000 V, 16 A, 0.5 mm² ... 4 mm², application: High-voltage

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1417408 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF62 |
| Product key | AF7ACE |
| GTIN | 4055626112732 |
| Weight per piece (including packing) | 55.8 g |
| Weight per piece (excluding packing) | 54 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

Technical data

Mounting

| | |
|---------------|--|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
| | Assembly procedure: <ul style="list-style-type: none">- Strip wire 9.5 mm,- connect the stripped part of the wire through the locking sleeve (for wire diameter > 3.2 mm),- crimp wire (with protracted locking sleeve) with CK2.5...ED crimp contact,- lock the locking sleeve with the crimp contact together with the module's insulating body. |

Product properties

| | |
|-------------------------|------------------------|
| Product type | Modular contact insert |
| Series | HC-M-HV |
| Application | High-voltage |
| Number of positions | 2 |
| Connection profile | 2 |
| Contact numbering | I, II |
| Number of module slots | 2 |
| No. of power contacts | 2 |
| No. of control contacts | 0 |
| Contact material type | turned |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Connection data


Connection technology

| | |
|-----------------------|------------------|
| Connection technology | Crimp connection |
|-----------------------|------------------|

Conductor connection

| | |
|---|---|
| Conductor cross-section | 0.5 mm ² ... 4 mm ² |
| Connection cross section AWG | 20 ... 12 |
| Stripping length of the individual wire | 9.5 mm |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 34.1 mm |
| Height | 61.3 mm |

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

| | |
|--------|---------|
| Length | 29.3 mm |
|--------|---------|

Mechanical characteristics

| | |
|------------------------|--------|
| Minimum housing height | 72 mm |
| Contact diameter | 2.5 mm |

Electrical properties

| | |
|----------------------------------|------------------------------|
| Rated voltage (III/3) | 2900 V (Conductor-PE) |
| | 5000 V (Conductor-Conductor) |
| Rated voltage for power contacts | 2900/5000 V |
| Rated surge voltage | 15 kV |
| Rated current | 16 A |
| SCCR | 5 kA (UL 2237) |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Material specifications

| | |
|--|-----------------------|
| Flammability rating according to UL 94 | V0 |
| Contact material | Copper alloy |
| Contact surface material | Ag (alternatively Au) |
| Contact carrier material | PC |
| Standards/regulations | PC |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

Standards and regulations

Testing

| | |
|-----------------------|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|---|

HC-M-02-CT-M-HV-16 - Contact insert module





1417408


<https://www.phoenixcontact.com/us/products/1417408>


Drawings

Dimensional drawing



Schematic diagram





Derating diagram

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417408>

DNV

Approval ID: TAE000037S



CSA

Approval ID: 158887

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 600 V | 24 A | - 12 | - |



UL Recognized

Approval ID: E118976

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 600 V | 28 A | - 12 | - |



UL Recognized

Approval ID: E468743

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 600 V | 28 A | - | - |

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440217 |
| ECLASS-15.0 | 27440217 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

HC-M-02-CT-M-HV-16 - Contact insert module



1417408

<https://www.phoenixcontact.com/us/products/1417408>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 5.333 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com