

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable



1417589

<https://www.phoenixcontact.com/us/products/1417589>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-pos., PVC, RAL 7021 (black gray), free cable end to angled M8 socket, cable length: 0.43 m

## Commercial data

Item number	1417589
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1BCA
GTIN	4055626117607
Weight per piece (including packing)	18.27 g
Weight per piece (excluding packing)	16.38 g
Country of origin	DE

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable

1417589

<https://www.phoenixcontact.com/us/products/1417589>

## Technical data

### Product properties


Product type	Sensor/actuator cable
--------------	-----------------------

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Cable/line

#### PVC black [PVC]

Dimensional drawing	
Cable weight	33 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross-section	4x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	22 mm

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable



1417589

<https://www.phoenixcontact.com/us/products/1417589>

Flame resistance	As per UL-Style 2464
Resistance to oil	EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable





1417589

<https://www.phoenixcontact.com/us/products/1417589>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417589>

 <b>UL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	-	-

 <b>cUL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	-	-

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable



1417589

<https://www.phoenixcontact.com/us/products/1417589>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-4P-0,43-PVC/M 8FR BK - Sensor/actuator cable



1417589

<https://www.phoenixcontact.com/us/products/1417589>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)