

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting



1417853

<https://www.phoenixcontact.com/us/products/1417853>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Pin, straight, M12-SPEEDCON, A-coding, on free cable end, Individual wires, cable length: 1 m, 0.25 mm², potted, this item is expected to be lead-free from Q3 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1417853
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCGA
GTIN	4055626128542
Weight per piece (including packing)	36.4 g
Weight per piece (excluding packing)	33.421 g
Customs tariff number	85444290
Country of origin	DE

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting



1417853

<https://www.phoenixcontact.com/us/products/1417853>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery
General	Contact connection method: Crimp connection

Mounting

Mounting type	Rear mounting (M12 x 1)
---------------	-------------------------

Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	8
Coding	A
Thread type	M12

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Molding compound	PUR (potted)

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Pin
Conductor cross-section	0.25 mm ²

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting



1417853

<https://www.phoenixcontact.com/us/products/1417853>

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	1 m
Cable cross section	0.25 mm ²
AWG signal line	24

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
UL Type Rating	Type 4 (indoor use only)


SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting

1417853

<https://www.phoenixcontact.com/us/products/1417853>

Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting




1417853

<https://www.phoenixcontact.com/us/products/1417853>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417853>

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	24	-

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	24 - 22	-

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting



1417853

<https://www.phoenixcontact.com/us/products/1417853>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-MS-8CON-M12/1,0 SCO - Device connector rear mounting



1417853

<https://www.phoenixcontact.com/us/products/1417853>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com