

SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting



1421741

<https://www.phoenixcontact.com/us/products/1421741>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, straight, M12-Standard, B-coding, Wave soldering, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1421741
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	AB26
Product key	ABQEOL
GTIN	4055626282572
Weight per piece (including packing)	16.12 g
Weight per piece (excluding packing)	14.3 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting



1421741

<https://www.phoenixcontact.com/us/products/1421741>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting (Pg9)
---------------	---------------------

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Coding	B
Thread type	M12

Material specifications

Material Housing	V4A
Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

Connection data

Conductor connection	
Connection method	Wave soldering
Contact connection type	Pin

Connector

Connection 1	
Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	Standard
Coding	B

Environmental and real-life conditions

Ambient conditions	
UL Type Rating	Type 4 (indoor use only)


SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting

1421741

<https://www.phoenixcontact.com/us/products/1421741>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting





1421741


<https://www.phoenixcontact.com/us/products/1421741>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1421741>

 cUL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	22	-

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	22	-

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting



1421741

<https://www.phoenixcontact.com/us/products/1421741>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12MSB-5CON-L180 VA - Device connector rear mounting



1421741

<https://www.phoenixcontact.com/us/products/1421741>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com