

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable



1418855

<https://www.phoenixcontact.com/us/products/1418855>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Sensor/actuator cable, PUR halogen-free, black RAL 9005, 12-wire, color single wire: white, brown, green, yellow, gray, pink, blue, red, black, violet, gray/pink, red/blue

Commercial data

Item number	1418855
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4055626157351
Weight per piece (including packing)	5,893 g
Weight per piece (excluding packing)	5,893 g
Customs tariff number	85444290
Country of origin	DE

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable



1418855

<https://www.phoenixcontact.com/us/products/1418855>


Technical data

Product properties

Product type	Cable by the meter
Application	Standard
Number of positions	12

Cable/line

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	17 kg/km
Number of positions	12
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross-section	12x 0.14 mm ² (Signal line)
Wire diameter incl. insulation	1 mm ±0.05 mm (Signal line)
External cable diameter	7.20 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PP
Single wire, color	white, brown, green, yellow, gray, pink, blue, red, black, violet, gray/pink, red/blue
Overall twist	12 wires twisted in layers
Max. conductor resistance	142 Ω/km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 1500 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	36 mm
Smallest bending radius, movable installation	72 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 54 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable



1418855

<https://www.phoenixcontact.com/us/products/1418855>

Halogen-free	in accordance with DIN EN 50267-2-1
Flame resistance	in acc. to UL VW1
	DIN EN 60332-1-2
Resistance to oil	EN 60811-2-1
Other resistance	EN 50525-2-21:2012-01
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Low adhesion surface
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable




1418855

<https://www.phoenixcontact.com/us/products/1418855>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418855>

 UL Listed Approval ID: E221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1 A	-	-

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable



1418855

<https://www.phoenixcontact.com/us/products/1418855>

Classifications

ECLASS

ECLASS-15.0	27061801
ECLASS-13.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-12P-100,0-PUR/0,14 - Sensor/actuator cable



1418855

<https://www.phoenixcontact.com/us/products/1418855>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com