

VS-OE-OE-93G-100,0 - Data cable



1419152

<https://www.phoenixcontact.com/us/products/1419152>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Data cable, PROFINET CAT5 (100 Mbps), EtherCAT® CAT5 (100 Mbps), shielded, PVC/PVC, green RAL 6018, 4-wire (1x4xAWG22/7, SF/TQ), color single wire: white, yellow, blue, orange, cable length: 100 m

Commercial data

Item number	1419152
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356540766
Weight per piece (including packing)	6,416 g
Weight per piece (excluding packing)	6,235 g
Customs tariff number	85444290
Country of origin	DE

VS-OE-OE-93G-100,0 - Data cable

1419152

<https://www.phoenixcontact.com/us/products/1419152>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	4
Shielded	yes

Electrical properties

Transmission medium	Copper
Transmission speed	100 Mbps


Interfaces

Signal type/category	EtherCAT® CAT5 (IEC 11801:2002), 100 Mbps
----------------------	-------------------------------------------

Cable/line

Cable length	100 m
--------------	-------

PROFINET PVC stranded CAT5 [93B]

Dimensional drawing	
UL AWM Style	21695 (80 °C / 600 V)
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
AWG signal line	22
Conductor cross-section	4x 0.34 mm ²
Wire diameter incl. insulation	1.5 mm ±0.1 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Overall twist	Star quad
Optical shield covering	85 %
Insulation resistance	≥ 5 GΩ*km
Loop resistance	≤ 120.00 Ω/km

VS-OE-OE-93G-100,0 - Data cable



1419152

<https://www.phoenixcontact.com/us/products/1419152>

Wave impedance	100 Ω \pm 5 Ω (at 100 MHz)
Nominal voltage, cable	\leq 600 V
Test voltage Core/Core	2000 V ((50 Hz/1 min))
Test voltage Core/Shield	2000.00 V ((50 Hz/1 min))
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1685 (CSA FT 4)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 70 °C (Cable, flexible installation)

VS-OE-OE-93G-100,0 - Data cable



1419152

<https://www.phoenixcontact.com/us/products/1419152>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-OE-OE-93G-100,0 - Data cable



1419152

<https://www.phoenixcontact.com/us/products/1419152>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	51.051 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com