

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sercos III cable, shielded, star quad, AWG 22 stranded (7-wire), RAL 3020 (traffic red), RJ45 connector/IP67 push-pull, metal on RJ45 connector/IP67, metal, D-coded, length: 5 m

## Commercial data

Item number	1419178
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB11
Product key	ABNABA
GTIN	4046356541237
Weight per piece (including packing)	476.467 g
Weight per piece (excluding packing)	476.467 g
Customs tariff number	85444210
Country of origin	PL

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Application	Standard
Number of positions	4
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
----------------------	---

### Interfaces

Signal type/category	Sercos CAT5, 100 Mbps
----------------------	-----------------------

### Signaling

Status display	no
----------------	----

### Electrical properties

Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

### Mechanical properties

#### Mechanical data


Insertion/withdrawal cycles	≥ 250
-----------------------------	-------

### Material specifications

Outer sheath, material	PVC
Conductor material	Tin-plated Cu litz wires

### Connector

#### Connection 1

Dimensional drawing	
---------------------	---

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable




1419178

<https://www.phoenixcontact.com/us/products/1419178>

	Connector pin assignment plug RJ45
Type	RJ45 Plug, straight
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT® CAT5 (IEC 11801)
Insertion/withdrawal cycles	≥ 750
Insulation resistance	≥ 100 MΩ
Overvoltage category	I
Degree of pollution	2
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PC
Material Housing	PA-GF
Color (Housing)	gray
Flammability rating according to UL 94	V2
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

## Connection 2

Dimensional drawing	 <p>8 7 6 5 4 3 2 1</p>
	Connector pin assignment plug RJ45
Type	RJ45 Plug, straight
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT® CAT5 (IEC 11801)
Insertion/withdrawal cycles	≥ 750
Insulation resistance	≥ 100 MΩ
Overvoltage category	I
Degree of pollution	2
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PC
Material Housing	PA-GF
Color (Housing)	gray
Flammability rating according to UL 94	V2
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable




1419178

<https://www.phoenixcontact.com/us/products/1419178>

## Cable/line

Cable length	5.00 m
--------------	--------

### Sercos III [93K]

Dimensional drawing	
Cable weight	68 kg/km
UL AWM Style	21694 (60 °C / 600 V)
Number of positions	4
Shielded	yes
Cable type	Sercos III [93K]
Conductor structure	1x4xAWG22/7, SF/TQ
Signal runtime	5.3 ns/m
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup>
Wire diameter incl. insulation	approx. 1.55 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	signal red RAL 3020
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Thickness, outer sheath	approx. 0.90 mm
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	Star quad
Max. conductor resistance	≤ 120 Ω/km
Insulation resistance	≥ 0.5 GΩ*km
Coupling resistance	≤ 20.00 mΩ/m (at 10 Hz)
Wave impedance	100 Ω ±15 Ω (at 100 MHz)
Nominal voltage, cable	600 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	7 x D
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	46 mm

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

Flame resistance	according to UL 1685 (CSA FT 4)
Resistance to oil	Resistant to oil to a limited extent
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 70 °C (cable, fixed installation)
	-40 °C ... 70 °C (Cable, flexible installation)
Ambient temperature (installation)	-20 °C ... 60 °C

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-10 °C ... 60 °C (cable, fixed installation)
	-10 °C ... 60 °C (Cable, flexible installation)

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable


1419178

<https://www.phoenixcontact.com/us/products/1419178>



## Drawings

Circuit diagram



# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419178>



**EAC**

Approval ID: 19060508

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-PPC/ME-PPC/ME-93K-LI/5,0 - Patch cable



1419178

<https://www.phoenixcontact.com/us/products/1419178>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	1ab21918-c86b-42a6-b23d-5c0470d14d8c

### EF3.1 Climate Change

CO2e kg	7.426 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)