

# HC-STA-D07-CHWSCM-1TTP11-EL-AL - Housing



1419248

<https://www.phoenixcontact.com/us/products/1419248>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housings D7, with single locking latch, material: Die-cast aluminum, salt water resistant, protective cover material: PA, cable outlets: 1, straight, 1x Pg11, height: 60.5 mm, cable gland: none, protective cover: yes, Standard, for pin inserts

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1419248       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF56          |
| Product key                          | AF7APF        |
| GTIN                                 | 4055626159799 |
| Weight per piece (including packing) | 46.1 g        |
| Weight per piece (excluding packing) | 46.07 g       |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

1419248

<https://www.phoenixcontact.com/us/products/1419248>

## Technical data


### Notes

|         |   |
|---------|---|
| General | for contact inserts HC-A03, A04, D07, D08, Q02, Q03, Q04, Q05, Q07, Q12 |
|---------|---|

### Product properties

|                              |                            |
|------------------------------|----------------------------|
| Product type                 | Housing with locking latch |
| Housing type                 | Coupling housings          |
| Product family               | HC-STA-D07                 |
| Application                  | Standard                   |
| Type                         | D7                         |
| No. of cable outlets         | 1                          |
| Type of the screw connection | 1x Pg11                    |
| Protective cover             | yes                        |
| Shielded                     | no                         |
| Cable outlet                 | straight                   |
| Pg screw connection          | none                       |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 34.2 mm  |
| Height              | 60.5 mm  |
| Length              | 24.2 mm  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | V0 (Interlock)<br>V0 (Protective cover) |
| Housing material                       | Die-cast aluminum, salt water resistant |
| Housing surface material               | uncoated                                |
| Material, protective cover             | PA                                      |
| Locking latch material                 | PA                                      |

### Mechanical properties

#### Mechanical data

|                              |         |
|------------------------------|---------|
| Type of the screw connection | 1x Pg11 |
| Locking type                 | Latch   |

### Environmental and real-life conditions

# HC-STA-D07-CHWSCM-1TTP11-EL-AL - Housing



1419248

<https://www.phoenixcontact.com/us/products/1419248>

## Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP66              |
|                                 | IP67              |
| Enclosure rating (NEMA)         | 4 (UL 50e)        |
|                                 | 4X (UL 50e)       |
| Impact strength                 | IK06              |
| Ambient temperature (operation) | -40 °C ... 125 °C |

# HC-STA-D07-CHWSCM-1TTP11-EL-AL - Housing


1419248

<https://www.phoenixcontact.com/us/products/1419248>



## Drawings

Dimensional drawing



Dimensional drawing

1419248

<https://www.phoenixcontact.com/us/products/1419248>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000437 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

1419248

<https://www.phoenixcontact.com/us/products/1419248>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)