

# FOC-OP4S-OP4S-GL01/65 - Connecting cable



1419743

<https://www.phoenixcontact.com/us/products/1419743>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 4



## Product description

Robust connecting cable ODC-4 to ODC-4, with screw connection, degree of protection: IP68

## Your advantages

- Robust connector for 4 fibers, degree of protection: IP68 (when connected)
- For extreme ambient conditions

## Commercial data

Item number	1419743
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNHAA
GTIN	4055626187495
Weight per piece (including packing)	2,377.5 g
Weight per piece (excluding packing)	2,302.5 g
Country of origin	CN

1419743

<https://www.phoenixcontact.com/us/products/1419743>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	4

### Electrical properties

Attenuation	typ. 0.2 dB
	max. 0.6 dB
Transmission medium	Multi-mode fiberglass

### Mechanical properties

Tensile strength short-term/long-term	800 N
---------------------------------------	-------

### Material specifications

Flammability rating according to UL 94	V0
Ferrule material	TPU
Outer sheath, material	TPU

### Connector

#### Connection 1

Locking type	Screw locking mechanism
Handle color	black
Insertion/withdrawal cycles	1000
Degree of protection	IP68 (IEC 60529)
	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

#### Connection 2

Locking type	Screw locking mechanism
Handle color	black
Insertion/withdrawal cycles	1000
Degree of protection	IP68 (IEC 60529)
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

### Cable/line

Cable length	65 m
Cable weight	26.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Outer sheath, material	TPU
External sheath, color	black
Individual wire diameter	250 µm
Tensile strength short-term/long-term	800 N

# FOC-OP4S-OP4S-GL01/65 - Connecting cable



1419743

<https://www.phoenixcontact.com/us/products/1419743>

Halogen-free	complying with IEC 60754-1/2
--------------	------------------------------

## FO cable

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	Multi-mode fiberglass

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	100g, according to IEC 61300-2-9

# FOC-OP4S-OP4S-GL01/65 - Connecting cable



1419743

<https://www.phoenixcontact.com/us/products/1419743>

## Classifications

### ECLASS

ECLASS-13.0

27061003

### ETIM

ETIM 9.0

EC000438

### UNSPSC

UNSPSC 21.0

43223300

# FOC-OP4S-OP4S-GL01/65 - Connecting cable



1419743

<https://www.phoenixcontact.com/us/products/1419743>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)