

HC-M-RJ45-08-M - Contact insert module



1419887

<https://www.phoenixcontact.com/us/products/1419887>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: RJ45, type : RJ45, Pin, 48 V, 1 A, application: Data, With RJ45 contact insert

Commercial data

Item number	1419887
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4055626253251
Weight per piece (including packing)	14.4 g
Weight per piece (excluding packing)	13.4 g
Customs tariff number	85366990
Country of origin	PL

HC-M-RJ45-08-M - Contact insert module



1419887

<https://www.phoenixcontact.com/us/products/1419887>

Technical data

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-RJ45
Application	Data
Number of positions	8
Connection profile	RJ45
Contact numbering	1 - 8
Number of module slots	1

Insulation characteristics


Overvoltage category	III
Degree of pollution	3

Connection data

Conductor connection

Connection cross section AWG	24 ... 27 (flexible)
------------------------------	----------------------

Dimensions

Dimensional drawing	
Width	34.2 mm
Height	41 mm
Length	14.6 mm

Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	0.8 kV
Rated current	1 A
Nominal voltage U_N	50 V
Transmission characteristics (category)	CAT6 _A (IEC 60512-27-100:2008, TIA-568-C.2:2009)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

1419887

<https://www.phoenixcontact.com/us/products/1419887>

Material specifications

Flammability rating according to UL 94	V0
Contact material	Phosphor bronze
Contact surface material	Au
Contact carrier material	PC
Standards/regulations	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

Standards and regulations

Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---


HC-M-RJ45-08-M - Contact insert module




1419887

<https://www.phoenixcontact.com/us/products/1419887>

Drawings



RJ45 male insert



Contact insert module

HC-M-RJ45-08-M - Contact insert module



1419887

<https://www.phoenixcontact.com/us/products/1419887>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419887>

DNV

Approval ID: TAE000037S



CSA

Approval ID: 158887



UL Recognized

Approval ID: E118976

HC-M-RJ45-08-M - Contact insert module



1419887

<https://www.phoenixcontact.com/us/products/1419887>

Classifications

ECLASS

ECLASS-13.0	27440218
ECLASS-15.0	27440218

ETIM

ETIM 10.0	EC000438
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-RJ45-08-M - Contact insert module



1419887

<https://www.phoenixcontact.com/us/products/1419887>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.137 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com