

# SACCBP-FS-3P-M16/2,0-28R SCO - Flush-type connector



1422710

<https://www.phoenixcontact.com/us/products/1422710>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flush-type connector, 4-position, Cable, 0.50 mm<sup>2</sup>

## Commercial data

Item number	1422710
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	ABQYAA
GTIN	4055626314617
Weight per piece (including packing)	123.5 g
Weight per piece (excluding packing)	123.5 g
Country of origin	DE

# SACCBP-FS-3P-M16/2,0-28R SCO - Flush-type connector



1422710

<https://www.phoenixcontact.com/us/products/1422710>

## Technical data

### Notes

#### Safety note

##### Safety note

**WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the corresponding technical data. You will find information:

- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product

- Only use tools recommended by Phoenix Contact

- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

# SACCBP-FS-3P-M16/2,0-28R SCO - Flush-type connector



1422710

<https://www.phoenixcontact.com/us/products/1422710>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Product properties

Number of positions	4
Coding	A

## Insulation characteristics

Overvoltage category	II
Degree of pollution	3

## Electrical properties

Rated surge voltage	2.5 kV AC
Nominal voltage $U_N$	250 V
Nominal current $I_N$	4 A

## Connection data

Connection method	Cable
-------------------	-------

## Cable/line

Cable length	2
Cable cross section	0.5 mm <sup>2</sup>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (When plugged in) IP65 (When plugged in)
Ambient temperature (operation)	-25 °C ... 85 °C

## Standards and regulations

Standards/specifications	according to IEC 61076-2-101
--------------------------	------------------------------

## Mounting

Mounting type	Rear mounting (M16 x 1,5)
---------------	---------------------------

# SACCBP-FS-3P-M16/2,0-28R SCO - Flush-type connector



1422710

<https://www.phoenixcontact.com/us/products/1422710>

## Classifications

### UNSPSC

UNSPSC 21.0	39121413
-------------	----------

# SACCBP-FS-3P-M16/2,0-28R SCO - Flush-type connector



1422710

<https://www.phoenixcontact.com/us/products/1422710>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)