

SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set



1423414

<https://www.phoenixcontact.com/us/products/1423414>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sample set, Power, 5-position, Socket, straight, L-coding, THR solder connection

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

Commercial data

Item number	1423414
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABQXAA
GTIN	4055626345772
Weight per piece (including packing)	5.6 g
Weight per piece (excluding packing)	3.501 g
Country of origin	DE

SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set



1423414

<https://www.phoenixcontact.com/us/products/1423414>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Number of positions	5
Coding	L
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage U_N	63 V
Nominal current I_N	14 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Coding	L

Cable/line

SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set



1423414

<https://www.phoenixcontact.com/us/products/1423414>

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

Packaging specifications

Delivery state	with assembly pad
----------------	-------------------


SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set

1423414

<https://www.phoenixcontact.com/us/products/1423414>

Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

1423414
<https://www.phoenixcontact.com/us/products/1423414>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1423414>

 cULus Recognized Approval ID: E468743-20180113				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	63 V	16 A	-	-

SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set



1423414

<https://www.phoenixcontact.com/us/products/1423414>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set



1423414

<https://www.phoenixcontact.com/us/products/1423414>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com