

# HC-B24-I-TPT-F-48 - Contact insert

1423828

<https://www.phoenixcontact.com/us/products/1423828>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 24+PE, size: B24, power contacts: 24, control contacts: 0, number of connections per position: 2, Socket, Push-in connection, 500 V, 16 A, 0.25 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, application: Power

## Your advantages

- Easy installation without tools, even when mounted, with push-in connection technology
- Shortest installation time compared to other connection technologies
- Quick and effortless wiring, in particular when space is tight
- Automatic cabling with robots possible
- Safe wiring and operation with color-coded actuators
- Shock and vibration-resistant in accordance with DIN EN 61373
- Cost-effective and fast coding with plastic profiles
- Double conductor connection per pos.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1423828       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF61          |
| Product key                          | AF7ABC        |
| GTIN                                 | 4055626356266 |
| Weight per piece (including packing) | 111.6 g       |
| Weight per piece (excluding packing) | 111.6 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | CN            |

# HC-B24-I-TPT-F-48 - Contact insert



1423828

<https://www.phoenixcontact.com/us/products/1423828>

## Technical data

### Notes

|         |   |
|---------|---|
| General | Use only flexible conductors with ferrule (in conjunction with CRIMPFOX 6 only) |
| General | Connectors may be operated only when there is no load/voltage.                  |

### Mounting

|               |   |
|---------------|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|---|


### Product properties

|                                    |  |
|------------------------------------|--|
| Product type                       | Contact insert with a fixed no. of positions |
| Series                             | HC-B   |
| Application                        | Power  |
| Type                               | B24<br>B48                                   |
| Number of positions                | 24   |
| Connection profile                 | 24+PE  |
| Contact numbering                  | 25 - 48                                      |
| Number of connections per position | 2  |
| No. of power contacts              | 24   |
| No. of control contacts            | 0  |
| Contact material type              | rolled                                       |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Width                           | 34 mm  |
| Height                          | 34.6 mm  |
| Length                          | 111 mm   |
| Drill hole distance, horizontal | 104 mm   |

### Mechanical characteristics

|                  |        |
|------------------|--------|
| Contact diameter | 2.5 mm |
|------------------|--------|

### Connection data

Connection technology

# HC-B24-I-TPT-F-48 - Contact insert



1423828

<https://www.phoenixcontact.com/us/products/1423828>

|                                    |                    |
|------------------------------------|--------------------|
| Connection technology              | Push-in connection |
| Number of connections per position | 2                  |

## Conductor connection

|   |  |
|---|--|
| Conductor cross-section                 | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                             |
| Connection cross section AWG            | 24 ... 16  |
| Tightening torque                       | 0.8 Nm ... 1.2 Nm (PE connection)  |
|   | 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing) |
| Stripping length of the individual wire | 8 mm ±1 mm   |

## Electrical properties

|                       |       |
|-----------------------|-------|
| Rated voltage (III/3) | 500 V |
| Rated surge voltage   | 6 kV  |
| Rated current         | 16 A  |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

## Material specifications

|  |              |
|--|--------------|
| Flammability rating according to UL 94 | V0           |
| Contact material                       | Copper alloy |
| Contact surface material               | Ag           |
| Contact carrier material               | PC           |
| Standards/regulations                  | PC           |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

## Standards and regulations

|  |              |
|--|--------------|
| Constructional and testing regulations | DIN EN 61984 |
|  | DIN EN 60664 |
|  | IEC 60352    |
| Tests                                  | DIN EN 61984 |
|  | DIN EN 60664 |
|  | IEC 60352    |

### Testing

|                       |   |
|-----------------------|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|---|


# HC-B24-I-TPT-F-48 - Contact insert

1423828

<https://www.phoenixcontact.com/us/products/1423828>


## Drawings

Dimensional drawing



Female insert

Dimensional drawing



Mounting cutout when used without housing


# HC-B24-I-TPT-F-48 - Contact insert



1423828


<https://www.phoenixcontact.com/us/products/1423828>

Schematic diagram



Connector pin assignment, connection side

Diagram



Derating diagram

# HC-B24-I-TPT-F-48 - Contact insert



1423828

<https://www.phoenixcontact.com/us/products/1423828>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1423828>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 13631

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 10 A                  | - 16              | -                           |



### UL Recognized

Approval ID: E118976

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 13 A                  | - 16              | -                           |

# HC-B24-I-TPT-F-48 - Contact insert



1423828

<https://www.phoenixcontact.com/us/products/1423828>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440205 |
| ECLASS-15.0 | 27440205 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# HC-B24-I-TPT-F-48 - Contact insert



1423828

<https://www.phoenixcontact.com/us/products/1423828>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)