

# HC-M-06-PT-M - Contact insert module



1424225

<https://www.phoenixcontact.com/us/products/1424225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 6, power contacts: 6, control contacts: 0, Pin, Push-in connection, 500 V, 16 A, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Power

## Your advantages

- Easy installation without tools, even when mounted, with push-in connection technology
- Shortest installation time compared to other connection technologies
- Quick and effortless wiring, in particular when space is tight
- Automatic cabling with robots possible
- Safe wiring and operation with color-coded actuators
- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1424225
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4055626369563
Weight per piece (including packing)	19.99 g
Weight per piece (excluding packing)	18.3 g
Customs tariff number	85366990
Country of origin	CN

# HC-M-06-PT-M - Contact insert module



1424225

<https://www.phoenixcontact.com/us/products/1424225>

## Technical data

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

### Product properties

Product type	Modular contact insert
Series	HC-M-06
Application	Power
Number of positions	6
Connection profile	6
Contact numbering	1 - 6
Number of module slots	1
No. of power contacts	6
No. of control contacts	0
Contact material type	turned

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Connection data


#### Connection technology

Connection technology	Push-in connection
-----------------------	--------------------

#### Conductor connection

Conductor cross-section	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection cross section AWG	20 ... 14
Stripping length of the individual wire	10 mm

### Dimensions

Dimensional drawing	
Width	34.1 mm
Height	39 mm
Length	14.6 mm

### Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

### Electrical properties

# HC-M-06-PT-M - Contact insert module



1424225

<https://www.phoenixcontact.com/us/products/1424225>

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	16 A (power contacts)
SCCR	5 kA (UL 2237)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


# HC-M-06-PT-M - Contact insert module



1424225


<https://www.phoenixcontact.com/us/products/1424225>

## Drawings



Dimensional drawing

Dimensional drawing




# HC-M-06-PT-M - Contact insert module

1424225

<https://www.phoenixcontact.com/us/products/1424225>




Schematic diagram




Connector pin assignment, connection side

1424225

<https://www.phoenixcontact.com/us/products/1424225>



Derating diagram for flexible conductors



Derating diagram for flexible conductors with ferrule

# HC-M-06-PT-M - Contact insert module




1424225

<https://www.phoenixcontact.com/us/products/1424225>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424225>

 <b>UL Recognized</b> Approval ID: E468743				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	600 V	16 A	- 14	-

# HC-M-06-PT-M - Contact insert module



1424225

<https://www.phoenixcontact.com/us/products/1424225>

## Classifications

### ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

### ETIM

ETIM 10.0	EC000438
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-M-06-PT-M - Contact insert module



1424225

<https://www.phoenixcontact.com/us/products/1424225>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)