

# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type socket, 3-pos., M8, rear/screw mounting with M12 thread, with 3 m PUR cable, 3 x 0.25 mm<sup>2</sup>

## Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- Standard pin assignments and codings for signal transmission with a uniform design-in design

## Commercial data

Item number	1424316
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB28
Product key	ABQIDC
GTIN	4046356729123
Weight per piece (including packing)	106.5 g
Weight per piece (excluding packing)	106.5 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

## Technical data

### Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	--

### Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR/PA 6.6
Material for screw connection	Brass, nickel-plated
Conductor material	Tin-plated Cu litz wires

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	Individual wires
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
-------------	--------

# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Head cable outlet	straight
Head thread type	M8
Coding	A

## Connection 2

Head design	free cable end
-------------	----------------

## Cable/line

Cable length	3 m
Cable type	PUR
Single wire, color	brown, blue, black
Conductor material	Tin-plated Cu litz wires
AWG signal line	24
Material wire insulation	TPE

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Socket)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104


# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting

1424316

<https://www.phoenixcontact.com/us/products/1424316>

## Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

## Classifications

### ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

### ETIM

ETIM 10.0	EC003570
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)