

# SAC-3P-24AWG-OE-OE-542-300,0SH - Cable reel



1422007

<https://www.phoenixcontact.com/us/products/1422007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, shielded, PVC, yellow, 3-wire, color single wire: brown, blue, black, cable length: 300 m

## Commercial data

Item number	1422007
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF16
Product key	AF1IIB
GTIN	4055626324722
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444995
Country of origin	US

1422007

<https://www.phoenixcontact.com/us/products/1422007>

## Technical data


### Product properties

Product type	Cable by the meter
Application	Connector
Number of positions	3

### Cable/line

Cable length	300 m
--------------	-------

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	33 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	yes
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.20 mm
AWG signal line	24
Wire diameter incl. insulation	1.12 mm ±0.03 mm
External cable diameter	4.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Optical shield covering	85 %
Max. conductor resistance	max. 79.7 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, movable installation	57 mm
Flame resistance	FT4
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation)

# SAC-3P-24AWG-OE-OE-542-300,0SH - Cable reel



1422007

<https://www.phoenixcontact.com/us/products/1422007>

---

-5 °C ... 105 °C (Cable, flexible installation)

# SAC-3P-24AWG-OE-OE-542-300,0SH - Cable reel



1422007

<https://www.phoenixcontact.com/us/products/1422007>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

# SAC-3P-24AWG-OE-OE-542-300,0SH - Cable reel



1422007

<https://www.phoenixcontact.com/us/products/1422007>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)