

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type socket, 3-pos., M8, rear/screw mounting with M12 thread, with 3 m PUR cable, 3 x 0.25 mm²

Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1424316
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB28
Product key	ABQIDC
GTIN	4046356729123
Weight per piece (including packing)	106.5 g
Weight per piece (excluding packing)	106.5 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Technical data

Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	--

Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR/PA 6.6
Material for screw connection	Brass, nickel-plated
Conductor material	Tin-plated Cu litz wires

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
-------------	--------

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Head cable outlet	straight
Head thread type	M8
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	3 m
Cable type	PUR
Single wire, color	brown, blue, black
Conductor material	Tin-plated Cu litz wires
AWG signal line	24
Material wire insulation	TPE

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Socket)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting

1424316

<https://www.phoenixcontact.com/us/products/1424316>

Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M8FS-3CON-M12/3,0 PUR - Device connector rear mounting



1424316

<https://www.phoenixcontact.com/us/products/1424316>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.1 Climate Change

CO2e kg	1.622 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com