HC-CIF-D25-AIWS-SM-NI - Adapter insert

1424341

https://www.phoenixcontact.com/us/products/1424341

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Adapter insert, design: D25

Product description

HC-A10, HC-A16, HC-D15, HC-D25 mounting adapters

Commercial data

Item number	1424341
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF60
Product key	AF7AHZ
GTIN	4055626370781
Weight per piece (including packing)	17.175 g
Weight per piece (excluding packing)	17 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Notes

General	Protection against electric shock must be ensured by the user. The continuity of the PE connection must be verified and satisfied by the user. The PE connection must be implemented equilaterally.

Product properties

Product type	Adapter
Application	Adapter for contact inserts
Type	D25

Material specifications

Material	Steel, galvanized


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C

Drawings

Dimensional drawing



Dimensional drawing

Classifications

ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440192

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com