

# SAC-8P-0,25-OE-OE-240-100,0 US - Cable reel



1422052

<https://www.phoenixcontact.com/us/products/1422052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, PUR halogen-free, yellow, 8-wire, color single wire: white, brown, green, yellow, gray, pink, blue, red, cable length: 100 m

## Commercial data

Item number	1422052
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF16
Product key	AF1IIA
GTIN	4055626338132
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444995
Country of origin	DE

# SAC-8P-0,25-OE-OE-240-100,0 US - Cable reel



1422052

<https://www.phoenixcontact.com/us/products/1422052>

## Technical data

### Product properties

Product type	Cable by the meter
Application	Connector
Number of positions	8


### Electrical properties

Nominal voltage $U_N$	300 V
-----------------------	-------

### Cable/line

Cable length	100 m
--------------	-------

### PUR halogen-free yellow [240]

Dimensional drawing	
Cable weight	46 kg/km
UL AWM Style	20549
Number of positions	8
Shielded	no
Cable type	PUR halogen-free yellow [240]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	8x 0.25 mm <sup>2</sup>
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	5.90 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	yellow
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.80 mm
Overall twist	8 wires around filler to the core
Length of twist, overall twist	70 mm
Max. conductor resistance	78 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC

# SAC-8P-0,25-OE-OE-240-100,0 US - Cable reel



1422052

<https://www.phoenixcontact.com/us/products/1422052>

Test voltage	≥ 3000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
	in accordance with EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 100°C
	according to UL 758, 168 h at 60 °C
Other resistance	hydrolysis and microbe resistant
	Resistant to salt water
	abrasion-resistant
	Low adhesion
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

# SAC-8P-0,25-OE-OE-240-100,0 US - Cable reel



1422052

<https://www.phoenixcontact.com/us/products/1422052>

## Classifications

### ECLASS

ECLASS-15.0	27061801
ECLASS-13.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

1422052

<https://www.phoenixcontact.com/us/products/1422052>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)