

SAC-3P-0,34-OE-OE-240-300,0 SH - Cable reel



1422057

<https://www.phoenixcontact.com/us/products/1422057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, shielded, PUR halogen-free, yellow, 3-wire, color single wire: brown, blue, black, cable length: 300 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1422057 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF16 |
| Product key | AF1IIB |
| GTIN | 4055626325187 |
| Weight per piece (including packing) | 22.22 g |
| Weight per piece (excluding packing) | 22.22 g |
| Customs tariff number | 85444995 |
| Country of origin | DE |

1422057

<https://www.phoenixcontact.com/us/products/1422057>

Technical data

Product properties

| | |
|---------------------|--------------------|
| Product type | Cable by the meter |
| Application | Connector |
| Number of positions | 3 |


Electrical properties

| | |
|-----------------------|-------|
| Nominal voltage U_N | 300 V |
|-----------------------|-------|

Cable/line

| | |
|--------------|-------|
| Cable length | 300 m |
|--------------|-------|

PUR halogen-free yellow [240]

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Cable weight | 43 kg/km |
| UL AWM Style | 20549 |
| Number of positions | 3 |
| Shielded | yes |
| Cable type | PUR halogen-free yellow [240] |
| Conductor structure signal line | 42x 0.10 mm |
| AWG signal line | 22 |
| Conductor cross-section | 3x 0.34 mm ² |
| Wire diameter incl. insulation | 1.27 mm ±0.02 mm |
| External cable diameter | 5.90 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | yellow |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | brown, blue, black |
| Thickness, insulation | ≥ 0.21 mm |
| Thickness, outer sheath | approx. 1.20 mm |
| Overall twist | 3 wires, twisted |
| Length of twist, overall twist | 45 mm |
| Optical shield covering | 85 % |
| Max. conductor resistance | 58 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 1 GΩ*km (at 20 °C) |

SAC-3P-0,34-OE-OE-240-300,0 SH - Cable reel



1422057

<https://www.phoenixcontact.com/us/products/1422057>

| | |
|---|--|
| Nominal voltage, cable | ≤ 300 V AC |
| Test voltage | ≥ 3000 V AC (Spark test) |
| Test voltage Core/Shield | ≥ 2000.00 V AC (for 60 s) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 30 mm |
| Smallest bending radius, movable installation | 59 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 2000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ² |
| Halogen-free | in accordance with DIN VDE 0472 part 815 |
| | in accordance with EN 50267-2-1 |
| Flame resistance | in accordance with UL 758/1581 FT2 |
| Resistance to oil | According to DIN EN 60811-2-1, 168 h at 100°C |
| | according to UL 758, 168 h at 60 °C |
| Other resistance | hydrolysis and microbe resistant |
| | Resistant to salt water |
| | abrasion-resistant |
| | Low adhesion |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |
| | -25 °C ... 80 °C (Cable, flexible installation) |

SAC-3P-0,34-OE-OE-240-300,0 SH - Cable reel



1422057

<https://www.phoenixcontact.com/us/products/1422057>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27061801 |
| ECLASS-13.0 | 27061801 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003249 |
|----------|----------|

SAC-3P-0,34-OE-OE-240-300,0 SH - Cable reel



1422057

<https://www.phoenixcontact.com/us/products/1422057>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com