

VS-PPC-C1-RJ45-MNNA-8I10G - RJ45 connector



1422108

<https://www.phoenixcontact.com/us/products/1422108>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 8, CAT6_A, material: Metal, connection method: Crimp connection, connection cross section: AWG 27- 24, cable outlet: straight, color: silver, Ethernet

Commercial data

Item number	1422108
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAB
GTIN	4046356571982
Weight per piece (including packing)	69.1 g
Weight per piece (excluding packing)	65.9 g
Customs tariff number	85366990
Country of origin	DE

1422108

<https://www.phoenixcontact.com/us/products/1422108>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1 A
Nominal voltage U_N	48 V
Nominal current I_N	1 A
Transmission medium	Copper
Transmission characteristics (category)	CAT6 _A
Transmission speed	10 Gbps

Connection data

Connection technology

Connection method	Crimp connection
Connection cross section AWG	27 ... 24 (flexible)
Conductor cross-section	flexible

Dimensions

Width	22 mm
Height	30 mm
Length	57.7 mm

Material specifications

Color	silver
Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	Phosphor bronze

Cable/line

External cable diameter	5 mm ... 8 mm
-------------------------	---------------

VS-PPC-C1-RJ45-MNNA-8I10G - RJ45 connector



1422108

<https://www.phoenixcontact.com/us/products/1422108>

Cable cross section	0.14 mm ²
---------------------	----------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 250
-----------------------------	-------

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

VS-PPC-C1-RJ45-MNNA-8I10G - RJ45 connector



1422108

<https://www.phoenixcontact.com/us/products/1422108>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-C1-RJ45-MNNA-8I10G - RJ45 connector



1422108

<https://www.phoenixcontact.com/us/products/1422108>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	02948e2a-4cce-4ec2-87a4-b30c1ea51c9a

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com