VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector

1422205

https://www.phoenixcontact.com/us/products/1422205

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRIMP



RJ45 connector, RJ45, Ethernet, CAT6$_A$ (10 Gbps), 8-position, connection method: Crimp connection, material: Plastic, connection cross section: AWG 27- 24, degree of protection: IP65/IP67

Commercial data

Item number	1422205
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAB
GTIN	4046356571999
Weight per piece (including packing)	30.4 g
Weight per piece (excluding packing)	29.6 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1 A
Nominal voltage U_N	48 V
Nominal current I_N	1 A
Transmission medium	Copper
Transmission speed	10 Gbps
Transmission characteristics (category)	$CAT6_A$

Connection data

Connection technology

Connection method	Crimp connection
Connection cross section AWG	27 ... 24 (flexible)
Conductor cross-section	flexible

Interfaces

Signal type/category	Ethernet $CAT6_A$, 10 Gbps

Dimensions

Width	22 mm
Height	30 mm
Length	57.7 mm

Material specifications

Housing material	Plastic

Cable/line

External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 200

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-25 °C ... 60 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	673ec16f-b3d6-440a-ace2-55ae82a220b6

EF3.1 Climate Change

CO2e kg	0.676 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com