

NBC-100,0-1025 - Network cable



1422394

<https://www.phoenixcontact.com/us/products/1422394>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PROFINET power cable, 5x 2.5 mm², stranded (7-wire), outer sheath: PUR, outside diameter: 12.0 mm, RAL 7001 (silver gray), oil resistant, sold by the meter

Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

Commercial data

Item number	1422394
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNOIA
GTIN	4055626302058
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

NBC-100,0-1025 - Network cable



1422394

<https://www.phoenixcontact.com/us/products/1422394>

Technical data

Product properties

Product type	Data cable by the meter
Application	Flexible installation
Number of positions	5
Shielded	no

Electrical properties

Rated voltage (III/3)	750 V
Transmission medium	Copper

Interfaces

Signal type/category	PROFINET
----------------------	----------

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	Plastic

Cable/line

Cable length	100.00 m
Signal type/category	PROFINET
Outer sheath, material	Plastic

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (torsion capability)
	-40 °C ... 80 °C (torsion capability, drag chain capability)

NBC-100,0-1025 - Network cable



1422394

<https://www.phoenixcontact.com/us/products/1422394>

Classifications

ECLASS

ECLASS-13.0	27061801
-------------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NBC-100,0-1025 - Network cable



1422394

<https://www.phoenixcontact.com/us/products/1422394>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com