CUC-V14-C1ZNI-S/R4E8:10 - RJ45 connector

1422680

https://www.phoenixcontact.com/us/products/1422680

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IDC



RJ45 connector, RJ45, CAT5 (IEC 11801:2002) (1 Gbps), 8-position, connection method: IDC fast connection, material: Metal, connection cross section: AWG 26- 24, degree of protection: IP65/IP67

Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent release
- Protected data transmission thanks to 360° shielding concept
- Highest ESD and EMC resistance for reliable transmission

Commercial data

Item number	1422680
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AB17
Product key	ABNOAA
GTIN	4055626311425
Weight per piece (including packing)	97.26 g
Weight per piece (excluding packing)	88.419 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Frequency range	to 100 MHz
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Power transmission	PoE++ in accordance with: IEEE 802.3bt

Connection data

Connection technology

Connection method	IDC fast connection
Connection technology	QUICKON connection
Connection cross section AWG	26 ... 24 (solid)
	26 ... 24 (flexible)
Conductor cross-section	0.14 mm² ... 0.23 mm² (solid)
	0.14 mm² ... 0.25 mm² (flexible)

Dimensions

Width	22 mm
Height	34 mm
Length	80 mm

Material specifications

Flammability rating according to UL 94	V0

Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PC

Cable/line

External cable diameter	5.5 mm ... 10 mm
External cable diameter	5.5 mm ... 10 mm
Cable cross section	0.14 mm²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 40 °C

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1422680

cULus Recognized
Approval ID: E335024-20170228

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	56.5 V	1.75 A	-	-

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6bc3e79a-6920-4b19-b7fc-f9d1aaf97771

EF3.1 Climate Change

CO2e kg	2.861 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com