

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set



1422992

<https://www.phoenixcontact.com/us/products/1422992>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cat6_A flush-type socket, Ethernet, 8-pos., rear mounting, with straight solder connection



Commercial data

Item number	1422992
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABQAGS
GTIN	4055626323572
Weight per piece (including packing)	5.17 g
Weight per piece (excluding packing)	3.049 g
Country of origin	DE

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set



1422992

<https://www.phoenixcontact.com/us/products/1422992>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Shielded	yes
Coding	X
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$> 100 \text{ M}\Omega$
Nominal voltage U_N	50 V AC 60 V DC
Nominal current I_N	0.5 A
Transmission characteristics (category)	CAT6 _A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Material specifications

Material (Shield crossover)	GD-Zn
Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PPA

Connector

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set



1422992

<https://www.phoenixcontact.com/us/products/1422992>

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

Cable/line

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (when plugged in)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-109

Packaging specifications


Delivery state	with assembly pad
----------------	-------------------

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set

1422992

<https://www.phoenixcontact.com/us/products/1422992>

Drawings



Pin assignment M12 connector, 8-pos., view socket side

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set



1422992

<https://www.phoenixcontact.com/us/products/1422992>

Classifications

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CIM12FSX8CONL180THRSAMPLE - Sample set



1422992

<https://www.phoenixcontact.com/us/products/1422992>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8f30d0e8-5c24-409e-8af3-77a86051fab5

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com