

NBC-MSD/14,5-937/FSD SCO - Network cable



1423135

<https://www.phoenixcontact.com/us/products/1423135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), 4-position, PE-X halogen-free, black, Plug straight M12 SPEEDCON, coding: D / IP65, on Socket straight M12 SPEEDCON, coding: D / IP65, cable length: 14.5 m, Product tested according to customer specification/rail application

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1423135 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | AF1CJI |
| GTIN | 4055626326153 |
| Weight per piece (including packing) | 950.9 g |
| Weight per piece (excluding packing) | 950.9 g |
| Country of origin | PL |

1423135

<https://www.phoenixcontact.com/us/products/1423135>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Coding | D |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Interfaces

| | |
|----------------------|-------------------------------------|
| Bus system | PROFINET |
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|---|-----------------------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 4 A |
| Transmission medium | Copper |
| Transmission speed | 100 Mbps |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |

Material specifications

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Connector

Connection 1

| | |
|---------------------|---|
| Type | Plug straight M12 SPEEDCON / IP65 |
| Number of positions | 4 |
| Locking type | SPEEDCON |
| Coding type | D (Data) |
| Shielded | yes |
| Handle color | black |
| Material | CuSn (Contact) |
| | Ni/Au (Contact surface) |
| | PA (Contact carrier) |
| | TPU, hardly inflammable, self-extinguishing (Grip body) |
| | Zinc die-cast, nickel-plated (Screw connection) |

NBC-MSD/14,5-937/FSD SCO - Network cable



1423135

<https://www.phoenixcontact.com/us/products/1423135>

| | |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|


Connection 2

| | |
|----------------------|---|
| Type | Socket straight M12 SPEEDCON / IP65 |
| Locking type | SPEEDCON |
| Coding type | D (Data) |
| Shielded | yes |
| Handle color | black |
| Material | CuSn (Contact) Ni/Au (Contact surface) PA (Contact carrier) TPU, hardly inflammable, self-extinguishing (Grip body) Zinc die-cast, nickel-plated (Screw connection) |
| Degree of protection | IP65 |

Cable/line

| | |
|--------------|--------|
| Cable length | 14.5 m |
|--------------|--------|

PROFINET BETAtans® railway application CAT5 [939]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Cable weight | 71 kg/km |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PROFINET BETAtans® railway application CAT5 [939] |
| Conductor structure | 1x4xAWG22/7, SF/TQ |
| Signal runtime | 4.4 ns/m |
| Signal speed | 0.75 c |
| Conductor structure signal line | 7x 0.25 mm |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² |
| Wire diameter incl. insulation | 1.4 mm ±0.1 mm |
| External cable diameter | 6.60 mm ±0.2 mm |
| Outer sheath, material | PE-X |
| External sheath, color | black |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | Cell PE |
| Single wire, color | white-blue, orange-yellow |
| Thickness, outer sheath | 1.00 mm |

NBC-MSD/14,5-937/FSD SCO - Network cable



1423135

<https://www.phoenixcontact.com/us/products/1423135>

| | |
|--|--------------------------------------|
| Overall twist | Star quad |
| Max. conductor resistance | ≤ 54.4 Ω/km |
| Insulation resistance | ≥ 5 GΩ*km |
| Coupling resistance | < 13.00 mΩ/m (f = 1 MHz) |
| | < 8.00 mΩ/m (f = 10 MHz ... 100 MHz) |
| Wave impedance | 100 Ω ±5 Ω (f = 100 MHz) |
| Cable capacity | 44 nF/km (Line-line) |
| Cable impedance | 100 Ω ±15 Ω (f = 0.5 MHz ... 3 MHz) |
| Nominal voltage, cable | 125 V |
| Test voltage Core/Core | 1000 V AC (50 Hz, 1 min.) |
| Test voltage Core/Shield | 1000.00 V AC (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 6 x D |
| Smallest bending radius, fixed installation | 33 mm |
| Smallest bending radius, movable installation | 40 mm |
| Tensile strength | ≤ 60 N (temporary) |
| | ≤ 15 N (Permanent) |
| Near end crosstalk attenuation (NEXT) | 76 dB (with 1 MHz) |
| | 71 dB (at 4 MHz) |
| | 64 dB (at 10 MHz) |
| | 60 dB (at 16 MHz) |
| | 56 dB (at 31.25 MHz) |
| | 52 dB (at 62.5 MHz) |
| | 48 dB (at 100 MHz) |
| | 45 dB (at 155 MHz) |
| Power-summed near end crosstalk attenuation (PSNEXT) | 42 dB (at 200 MHz) |
| | 73 dB (with 1 MHz) |
| | 68 dB (at 4 MHz) |
| | 61 dB (at 10 MHz) |
| | 57 dB (at 16 MHz) |
| | 53 dB (at 31.25 MHz) |
| | 49 dB (at 62.5 MHz) |
| | 45 dB (at 100 MHz) |
| Return attenuation (RL) | 42 dB (at 155 MHz) |
| | 39 dB (at 200 MHz) |
| | 25 dB (with 1 MHz) |
| | 25 dB (at 4 MHz) |
| | 28 dB (at 10 MHz) |
| | 28 dB (at 16 MHz) |
| | 27 dB (at 31.25 MHz) |
| | 26 dB (at 62.5 MHz) |
| 25 dB (at 100 MHz) | |
| 25 dB (at 155 MHz) | |
| 23 dB (at 200 MHz) | |

1423135

<https://www.phoenixcontact.com/us/products/1423135>

| | |
|----------------------------------|---|
| Shield attenuation | 1.5 dB (with 1 MHz) |
| | 3.3 dB (at 4 MHz) |
| | 5.3 dB (at 10 MHz) |
| | 6.9 dB (at 16 MHz) |
| | 9.9 dB (at 31.25 MHz) |
| | 14.5 dB (at 62.5 MHz) |
| | 18.8 dB (at 100 MHz) |
| | 23.6 dB (at 155 MHz) |
| | 27.3 dB (at 200 MHz) |
| | 60.00 dB (up to 1000 MHz) |
| Halogen-free | in accordance with EN 50267-2-1 |
| | in accordance with EN 60684-2 |
| Flame resistance | in accordance with EN 60332-1-2 |
| | in accordance with EN 50266-2-5 |
| | in accordance with ISO 14572 5.21 (UN ECE-R 118.01) |
| Concentration of fumes | EN 61034-2 |
| Resistance to oil | in accordance with EN 50306-4, 72 hours at 100°C, IRM 902 |
| Fire protection in rail vehicles | BS 6853 (Internal cable Ia, Ib, II/external cable Ia, Ib, II) |
| | DIN 5510-2 (Fire protection level 1, 2, 3, 4) |
| | EN 45545-2 (Risk level HL1 - HL3) |
| | EN 50306-4 |
| | NF F16-101 (Classification C/F1) |
| | NF F16-101 (Internal cable A1, A2, B/external cable A1, A2, B) |
| | NFPA 130 |
| | PN-K-02511 |
| Other resistance | UIC 564-2 (Class A) |
| | Resistant to fuel (in accordance with EN 50306-4, 168 hours at 70°C, IRM 903) |
| Ambient temperature (operation) | Resistant to ozone (in accordance with EN 50306-4, 72 hours at 40°C, method B, volumetric concentration of 200×10^{-6}) |
| | -40 °C ... 85 °C (cable, fixed installation) |
| | -25 °C ... 70 °C (Cable, flexible installation) |
| | 160 °C (Short circuit) |

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |


Drawings

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

1423135

<https://www.phoenixcontact.com/us/products/1423135>

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

Schematic diagram




Pin assignment M12 socket, 4-pos., D-coded, female side

1423135

<https://www.phoenixcontact.com/us/products/1423135>

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

NBC-MSD/14,5-937/FSD SCO - Network cable



1423135

<https://www.phoenixcontact.com/us/products/1423135>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

1423135

<https://www.phoenixcontact.com/us/products/1423135>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com