

# SAC-3P- 3,0-PVC/FRS PE PPH DMG1 - Power cable



1423353

<https://www.phoenixcontact.com/us/products/1423353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 3-position, PVC, black, free cable end, on Socket angled M12 SPEEDCON, coding: S, cable length: 3 m, Customer version

## Commercial data

Item number	1423353
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	AF1CBB
GTIN	4055626347240
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

# SAC-3P- 3,0-PVC/FRS PE PPH DMG1 - Power cable



1423353

<https://www.phoenixcontact.com/us/products/1423353>

## Technical data

### Product properties

Product type	Power cable
Number of positions	3

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	230 V AC
	230 V DC
Nominal current $I_N$	12 A

### Connector

#### Connection 1

Type	free cable end
------	----------------


#### Connection 2

Type	Socket angled M12 SPEEDCON
Locking type	SPEEDCON
Coding type	S

### Cable/line

Cable length	3 m
--------------	-----

#### PVC black [PVC]

Dimensional drawing	
Cable weight	80 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure, voltage supply	30x 0.25 mm
AWG power supply	16
Conductor cross-section	3x 1.5 mm <sup>2</sup>

# SAC-3P- 3,0-PVC/FRS PE PPH DMG1 - Power cable



1423353

<https://www.phoenixcontact.com/us/products/1423353>

Wire diameter incl. insulation	2.4 mm ±0.1 mm
External cable diameter	6.80 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	≤ 13.3 Ω/km (at 20 °C)
Insulation resistance	≥ 10 MΩ*km (at 20 °C)
Nominal voltage, cable	300 V AC
Test voltage	2000 V AC
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	82 mm
Flame resistance	according to IEC 60332-1
	According to DIN EN 60332-1-2
	According to VW-1
	According to FT1
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 90 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67 (without preloading, as additional test in accordance with IEC 60529)
	IP68

# SAC-3P- 3,0-PVC/FRS PE PPH DMG1 - Power cable



1423353

<https://www.phoenixcontact.com/us/products/1423353>

## Classifications

### ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

### UNSPSC

UNSPSC 21.0	31251501
-------------	----------

1423353

<https://www.phoenixcontact.com/us/products/1423353>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)