

# SAC-4P-M12MSS/ 5,4-PUR/FSS PE - Power cable



1424735

<https://www.phoenixcontact.com/us/products/1424735>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: S, on Socket straight M12, coding: S, cable length: 5.4 m, for AC current up to 12 A/690 V

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special S-coding
- Our standard: robust halogen-free PUR cable

## Commercial data

Item number	1424735
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CCP
GTIN	4055626381060
Weight per piece (including packing)	636.6 g
Weight per piece (excluding packing)	636.6 g
Country of origin	DE

1424735

<https://www.phoenixcontact.com/us/products/1424735>

## Technical data

### Product properties

Product type	Power cable
Application	Energy supply
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	S

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	V0
Material of grip body	PP
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	690 V AC
Nominal current $I_N$	12 A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

### Connector

#### Connection 1

Type	Plug straight M12
Coding type	S (Power)

#### Connection 2

Type	Socket straight M12
Coding type	S (Power)

### Cable/line

Cable length	5.4 m
--------------	-------

PUR halogen-free black [PUR]

# SAC-4P-M12MSS/ 5,4-PUR/FSS PE - Power cable



1424735

<https://www.phoenixcontact.com/us/products/1424735>

Cable weight	92 kg/km
UL AWM Style	80°C/1000 V
Number of positions	4
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure, voltage supply	44x 0.20 mm
AWG power supply	16
Conductor cross-section	4x 1.5 mm <sup>2</sup>
Wire diameter incl. insulation	2.35 mm ±0.05 mm
External cable diameter	7.40 mm ±0.25 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, black 3, green/yellow
Thickness, insulation	≥ 0.31 mm
Thickness, outer sheath	approx. 0.85 mm
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 14.1 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 1000 V AC
Test voltage	≥ 10000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	37 mm
Smallest bending radius, movable installation	74 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: 500000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	According to UL 758/1581 (Cable Flame) in accordance with UL 758/1581 FT2 according to DIN EN 60332-2-2
Resistance to oil	according to DIN EN 60811-404, 168 h at 100 °C according to UL 758, 168 h at 60 °C
Other resistance	Hydrolysis and microbe resistant as per VDE 0282 section 10 Low adhesion abrasion-resistant Resistant to salt water
Ambient temperature (operation)	-50 °C ... 85 °C (cable, fixed installation) -30 °C ... 85 °C (Cable, flexible installation)

# SAC-4P-M12MSS/ 5,4-PUR/FSS PE - Power cable



1424735

<https://www.phoenixcontact.com/us/products/1424735>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67 (without preloading, as additional test in accordance with IEC 60529)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

# SAC-4P-M12MSS/ 5,4-PUR/FSS PE - Power cable




1424735

<https://www.phoenixcontact.com/us/products/1424735>

## Drawings



Plug, M12 x 1, straight



M12 x 1 socket, straight

1424735

<https://www.phoenixcontact.com/us/products/1424735>

Schematic diagram




M12 plug pin assignment, 4-pos., S-coded, plug side view

Schematic diagram




Pin assignment of M12 socket, 4-pos., S-coded, socket side view



Base curve

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

# SAC-4P-M12MSS/ 5,4-PUR/FSS PE - Power cable



1424735

<https://www.phoenixcontact.com/us/products/1424735>

## Classifications

### ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)