

SACC-CI-M12MS-17CON-L90 - Contact carrier



1424196

<https://www.phoenixcontact.com/us/products/1424196>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 17-position, Pin, angled, M12, A-coding, Wave soldering, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1424196
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAHM
GTIN	4046356692908
Weight per piece (including packing)	6.743 g
Weight per piece (excluding packing)	5.101 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12MS-17CON-L90 - Contact carrier



1424196

<https://www.phoenixcontact.com/us/products/1424196>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Number of positions	17
No. of control contacts	17
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	1.5 A

Connection data

Connection method	Wave soldering
-------------------	----------------

Signaling

Status display	no
Status display present	no

Material specifications

Material Contact carrier	PA 6T
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

Connector

Connection 1

SACC-CI-M12MS-17CON-L90 - Contact carrier



1424196

<https://www.phoenixcontact.com/us/products/1424196>

Head design	Pin
Head cable outlet	angled
Head thread type	M12
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67, when in locked state
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
	-40 °C ... 85 °C (without mechanical actuation)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Packaging specifications

Type of packaging	Blister
-------------------	---------

Drawings

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

SACC-CI-M12MS-17CON-L90 - Contact carrier



1424196

<https://www.phoenixcontact.com/us/products/1424196>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424196>

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	26	-

SACC-CI-M12MS-17CON-L90 - Contact carrier



1424196

<https://www.phoenixcontact.com/us/products/1424196>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1424196

<https://www.phoenixcontact.com/us/products/1424196>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4232bab7-9a56-46c8-a998-775d33340dd9

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com