

HC-M-04-PT-F - Contact insert module



1424220

<https://www.phoenixcontact.com/us/products/1424220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 4, power contacts: 4, control contacts: 0, Socket, Push-in connection, 830 V, 40 A, 2.5 mm² ... 6 mm², application: Power

Your advantages

- Easy installation without tools, even when mounted, with push-in connection technology
- Shortest installation time compared to other connection technologies
- Quick and effortless wiring, in particular when space is tight
- Automatic cabling with robots possible
- Safe wiring and operation with color-coded actuators
- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1424220 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF62 |
| Product key | AF7ACE |
| GTIN | 4055626369518 |
| Weight per piece (including packing) | 35 g |
| Weight per piece (excluding packing) | 35 g |
| Customs tariff number | 85366990 |
| Country of origin | CN |

HC-M-04-PT-F - Contact insert module



1424220

<https://www.phoenixcontact.com/us/products/1424220>

Technical data

Mounting

| | |
|---------------|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|---|

Product properties

| | |
|-------------------------|------------------------|
| Product type | Modular contact insert |
| Series | HC-M-04P |
| Application | Power |
| Number of positions | 4 |
| Connection profile | 4 |
| Number of module slots | 1 |
| No. of power contacts | 4 |
| No. of control contacts | 0 |
| Contact material type | rolled |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Connection data


Connection technology

| | |
|----------------------------------|--------------------|
| Connection technology | Push-in connection |
| Connection in acc. with standard | IEC / EN |

Conductor connection

| | |
|---|---|
| Conductor cross-section | 2.5 mm ² ... 6 mm ² |
| Connection cross section AWG | 14 ... 10 |
| Stripping length of the individual wire | 9.6 mm |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 33.4 mm |
| Height | 55.6 mm |
| Length | 14.8 mm |

Mechanical characteristics

| | |
|------------------------|-------|
| Minimum housing height | 72 mm |
| Contact diameter | 4 mm |

HC-M-04-PT-F - Contact insert module



1424220

<https://www.phoenixcontact.com/us/products/1424220>

Electrical properties

| | |
|--------------------------------|--------|
| Rated voltage (III/2) contacts | 1000 V |
| Rated voltage (III/3) | 830 V |
| Rated surge voltage (III/2) | 8 kV |
| Rated surge voltage (III/3) | 8 kV |
| Rated surge voltage | 8 kV |
| Rated current | 40 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Material specifications

| | |
|--|--------------|
| Flammability rating according to UL 94 | V0 |
| Contact material | Copper alloy |
| Contact surface material | Ag |
| Contact carrier material | PC |
| Standards/regulations | PC |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

Standards and regulations

Testing

| | |
|-----------------------|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|---|

HC-M-04-PT-F - Contact insert module




1424220

<https://www.phoenixcontact.com/us/products/1424220>

Drawings

Dimensional drawing



Dimensional drawing


HC-M-04-PT-F - Contact insert module

1424220

<https://www.phoenixcontact.com/us/products/1424220>



Schematic diagram




Connector pin assignment, connection side

1424220


<https://www.phoenixcontact.com/us/products/1424220>

Diagram



Derating diagram for flexible conductors

Diagram



Derating diagram for flexible conductors with ferrule

HC-M-04-PT-F - Contact insert module




1424220

<https://www.phoenixcontact.com/us/products/1424220>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424220>

|  cULus Recognized Approval ID: E468743 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 600 V | 30 A | - 10 | - |

HC-M-04-PT-F - Contact insert module



1424220

<https://www.phoenixcontact.com/us/products/1424220>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440217 |
| ECLASS-15.0 | 27440217 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

HC-M-04-PT-F - Contact insert module



1424220

<https://www.phoenixcontact.com/us/products/1424220>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com