

# HC-STA-D15-HHFS-1TTM25-ELC-AL - Housing



1424351

<https://www.phoenixcontact.com/us/products/1424351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing D15, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x M25, height: 68 mm, cable gland: none, Standard

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1424351       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF56          |
| Product key                          | AF7APE        |
| GTIN                                 | 4055626370873 |
| Weight per piece (including packing) | 127.1 g       |
| Weight per piece (excluding packing) | 120 g         |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

1424351

<https://www.phoenixcontact.com/us/products/1424351>

## Technical data

### Product properties

|                              |                            |
|------------------------------|----------------------------|
| Product type                 | Housing with locking latch |
| Housing type                 | Sleeve housing             |
| Product family               | HC-STA-D                   |
| Application                  | Standard                   |
| Type                         | D15                        |
| No. of cable outlets         | 1                          |
| Type of the screw connection | 1x M25                     |
| Cable outlet                 | straight                   |
| Pg screw connection          | none                       |

### Dimensions

|                     |   |
|---------------------|---|
| Dimensional drawing |  |
| Width               | 30 mm   |
| Height              | 68 mm   |
| Length              | 63.5 mm   |

### Material specifications

|                          |   |
|--------------------------|---|
| Seal material            | NBR, conductive                         |
| Housing material         | Die-cast aluminum, salt water resistant |
| Housing surface material | uncoated                                |

### Mechanical properties

#### Mechanical data

|                              |        |
|------------------------------|--------|
| Type of the screw connection | 1x M25 |
| Locking type                 | Pin    |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP66<br>IP67      |
| Impact strength                 | IK08              |
| Ambient temperature (operation) | -40 °C ... 125 °C |

# HC-STA-D15-HHFS-1TTM25-ELC-AL - Housing


1424351

<https://www.phoenixcontact.com/us/products/1424351>



## Drawings

Dimensional drawing




Dimensional drawing

1424351

<https://www.phoenixcontact.com/us/products/1424351>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424351>

### DNV

Approval ID: TAE000037S



### cUL Recognized

Approval ID: E255026



### UL Recognized

Approval ID: E255026

1424351

<https://www.phoenixcontact.com/us/products/1424351>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HC-STA-D15-HHFS-1TTM25-ELC-AL - Housing



1424351

<https://www.phoenixcontact.com/us/products/1424351>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)