

# HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housings D15, with single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x M20, height: 52 mm, cable gland: none, Standard

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1424359       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF56          |
| Product key                          | AF7APE        |
| GTIN                                 | 4055626371016 |
| Weight per piece (including packing) | 105.5 g       |
| Weight per piece (excluding packing) | 105.5 g       |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

# HC-STA-D15-CLWS-1TTM20-EL-AL - Housing

1424359

<https://www.phoenixcontact.com/us/products/1424359>

## Technical data


### Notes

|         |                                 |
|---------|---------------------------------|
| General | For contact inserts HC-D15, A10 |
|---------|---------------------------------|

### Product properties

|                              |                            |
|------------------------------|----------------------------|
| Product type                 | Housing with locking latch |
| Housing type                 | Coupling housings          |
| Product family               | HC-STA-D                   |
| Application                  | Standard                   |
| Type                         | D15                        |
| No. of cable outlets         | 1                          |
| Type of the screw connection | 1x M20                     |
| Cable outlet                 | straight                   |
| Pg screw connection          | none                       |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 30 mm  |
| Height              | 52 mm  |
| Length              | 63.5 mm  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | V0 (Interlock)                          |
| Housing material                       | Die-cast aluminum, salt water resistant |
| Housing surface material               | uncoated                                |
| Locking latch material                 | PA                                      |

### Mechanical properties

#### Mechanical data

|                              |        |
|------------------------------|--------|
| Type of the screw connection | 1x M20 |
| Locking type                 | Latch  |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP66              |
|                                 | IP67              |
| Impact strength                 | IK08              |
| Ambient temperature (operation) | -40 °C ... 125 °C |

# HC-STA-D15-CLWS-1TTM20-EL-AL - Housing


1424359

<https://www.phoenixcontact.com/us/products/1424359>



## Drawings

Dimensional drawing



Dimensional drawing

1424359

<https://www.phoenixcontact.com/us/products/1424359>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424359>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026

1424359

<https://www.phoenixcontact.com/us/products/1424359>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

1424359

<https://www.phoenixcontact.com/us/products/1424359>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)