

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 8-position, Plug straight M12, coding: A, Insulation displacement connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 3 mm ... 7 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1424433       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF31          |
| Product key                          | AF2CCA        |
| GTIN                                 | 4055626375625 |
| Weight per piece (including packing) | 20.9 g        |
| Weight per piece (excluding packing) | 20 g          |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Sensor type          | Universal                       |
| Number of positions  | 8                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                          |  |
|--------------------------|--|
| Dimensional drawing      |  |
| Length                   | 60 mm  |
| Wrench size, union nut   | 16 mm  |
| Wrench size, counter nut | 15 mm  |

### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 3 mm ... 7 mm |
|------------------|---------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 20 mm |
|------------------|-------|

### Material specifications

|  |                              |
|--|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Seal material                          | FKM                          |
| Material of grip body                  | PA-GF                        |
| Contact material                       | CuSn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA 6.6                       |
| Material for screw connection          | Zinc die-cast, nickel-plated |
| Wire insulation material               | PVC / PE / PP / rubber       |

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

## Connection data

### Conductor connection

|                              |  |
|------------------------------|--|
| Connection method            | Insulation displacement connection                       |
| Connection cross section     | 0.14 mm <sup>2</sup> ... 0.25 mm <sup>2</sup> (flexible) |
| Connection cross section AWG | 26 ... 24 (flexible)                                     |
| Tightening torque            | 0.4 Nm (M12 knurl)<br>4 Nm (Pressure nut)                |

### Connection assignment

|   |        |
|---|--------|
| Contact   Color (signal designation)   Contact (optional) | 1 = WH |
|   | 2 = BN |
|   | 3 = GN |
|   | 4 = YE |
|   | 5 = GY |
|   | 6 = PK |
|   | 7 = BU |
|   | 8 = RD |

## Electrical properties

|                                |                    |
|--------------------------------|--------------------|
| Rated surge voltage            | 0.8 kV             |
| Insulation resistance          | ≥ 100 MΩ           |
| Nominal voltage U <sub>N</sub> | 30 V AC<br>30 V DC |
| Nominal current I <sub>N</sub> | 2 A                |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | A        |

## Cable/line

|                      |           |
|----------------------|-----------|
| Signal type/category | Universal |
|----------------------|-----------|

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |
| Ambient temperature (assembly)  | -5 °C ... 50 °C                  |

## Standards and regulations

### M12

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 connector                |
| Standards/specifications | according to IEC 61076-2-101 |


# SACC-M12MS-8QO-0,25-CM M - Connector

1424433

<https://www.phoenixcontact.com/us/products/1424433>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight

Functional drawing



1424433

<https://www.phoenixcontact.com/us/products/1424433>

Schematic diagram



Pin assignment of M12 plug, 8-pos., A-coded, view of plug side

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12MS-8QO-0,25-CM M - Connector



1424433

<https://www.phoenixcontact.com/us/products/1424433>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)