

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5 (1 Gbps), 8-position, PUR halogen-free, water blue RAL 5021, shielded, Plug straight RJ45 / IP20, on Plug straight RJ45, cable length: 5.9 m

## Commercial data

Item number	1425323
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CMI
GTIN	4055626389721
Weight per piece (including packing)	303 g
Weight per piece (excluding packing)	290 g
Country of origin	PL

1425323

<https://www.phoenixcontact.com/us/products/1425323>

## Technical data

### Product properties

Product type	Data cable preassembled
Application	Standard
Number of positions	8
Shielded	yes
Coding	A

### Interfaces

Bus system	Ethernet
Signal type/category	Ethernet CAT5 (based on IEC 11801), 1 Gbps

### Signaling

Status display	no
Status display present	no

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	1 A
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

### Material specifications

Seal material	NBR
---------------	-----

### Connector

#### Connection 1

Type	Plug straight RJ45 / IP20
Number of positions	8 (8)
Handle color	gray
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PC (Contact carrier)
	PA (Housing)
Degree of protection	IP20

#### Connection 2

Type	Plug straight RJ45
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PC (Contact carrier)

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323


<https://www.phoenixcontact.com/us/products/1425323>

	PA (Housing)
--	--------------

## Cable/line

Cable length	5.9 m
--------------	-------

### Ethernet flexible CAT5, 4-pair [94B]

Dimensional drawing	
UL AWM Style	21238 (80 °C / 600 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet flexible CAT5, 4-pair [94B]
Conductor structure	4x2xAWG26/7, SF/UTP
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	0.96 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Optical shield covering	70 %
Insulation resistance	≥ 500 MΩ*km
Loop resistance	≤ 290.00 Ω/km
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	51 mm
Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

	according to CSA C 22.2 No. 210-FT1
Resistance to oil	in accordance with EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67/IP20
Ambient temperature (operation)	-25 °C ... 90 °C (M12 connector)
Ambient temperature (operation) (male connector/female connector)	-20 °C ... 70 °C (RJ45 connector)

## Standards and regulations

### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

## Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Dimensional drawing



RJ45 connector, IP20

# NBC-M12FS/5,9-94B/R4AC - Network cable

1425323

<https://www.phoenixcontact.com/us/products/1425323>



Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

# NBC-M12FS/5,9-94B/R4AC - Network cable

1425323

<https://www.phoenixcontact.com/us/products/1425323>



Schematic diagram



Connector pin assignment plug RJ45


# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

Circuit diagram



Contact assignment of the M12 and RJ45 plug

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1425323>

 <b>UL Listed</b> Approval ID: FILE E 335024				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	0.5 A	-	-

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# NBC-M12FS/5,9-94B/R4AC - Network cable



1425323

<https://www.phoenixcontact.com/us/products/1425323>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)