

SACC-M 8FS-4QO-0,5-VA - Connector



1426316

<https://www.phoenixcontact.com/us/products/1426316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, 4-position, Socket straight M8, coding: A, Insulation displacement connection, knurl material: Stainless steel 1.4305, external cable diameter 2.5 mm ... 5 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1426316 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF31 |
| Product key | AF2BCA |
| GTIN | 4055626457666 |
| Weight per piece (including packing) | 6.8 g |
| Weight per piece (excluding packing) | 6.7 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-M 8FS-4QO-0,5-VA - Connector



1426316

<https://www.phoenixcontact.com/us/products/1426316>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Dimensions

External dimensions

| | |
|------------------|-------------------------|
| Outside diameter | 2.5 mm ... 5 mm ±0.2 mm |
|------------------|-------------------------|

Material specifications

| | |
|--|------------------------|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | PA 6 |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Stainless steel 1.4305 |
| Wire insulation material | PVC / PE / PP / rubber |

Connection data

Conductor connection

| | |
|------------------------------|--|
| Connection method | Insulation displacement connection |
| Connection cross section | 0.25 mm ² ... 0.5 mm ² |
| Connection cross section AWG | 24 ... 20 |
| Tightening torque | 0.6 Nm (Pressure nut) |
| | 0.2 Nm (M8 knurl) |

Electrical properties

| | |
|--------------------|--------|
| Contact resistance | ≤ 5 mΩ |
|--------------------|--------|

SACC-M 8FS-4QO-0,5-VA - Connector



1426316

<https://www.phoenixcontact.com/us/products/1426316>

| | |
|--------------------------------|----------|
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 30 V AC |
| | 30 V DC |
| Nominal current I _N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M8 |
| Coding | A |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 2.5 mm ... 5 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| | IP69K |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 80 °C (Plug / socket) |

Standards and regulations

M8

| | |
|--------------------------|-----------------|
| Standard designation | M8 connector |
| Standards/specifications | IEC 61076-2-104 |


SACC-M 8FS-4QO-0,5-VA - Connector

1426316

<https://www.phoenixcontact.com/us/products/1426316>


Drawings

Dimensional drawing



Socket M8 x 1, straight

Functional drawing




SACC-M 8FS-4QO-0,5-VA - Connector

1426316

<https://www.phoenixcontact.com/us/products/1426316>



Schematic diagram



Pin assignment of M8 socket, 4-pos., view of pin side

SACC-M 8FS-4QO-0,5-VA - Connector



1426316

<https://www.phoenixcontact.com/us/products/1426316>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-M 8FS-4QO-0,5-VA - Connector



1426316

<https://www.phoenixcontact.com/us/products/1426316>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 1.01 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com